






NOTES:
 1. FOR USE WITH RG-58, 142, 225 & 400/U CABLE GROUPS.
 2. FOR CABLES INSTRUCTIONS SEE CP-1004.

UNLESS OTHERWISE SPECIFIED:
 1. TOLERANCES: FRACTIONS & 2 PLACE DECIMALS & C/O
 2. PLACE DECIMALS & 3 PLACE DECIMALS & C/O
 3. SURFACE ROUGHNESS 32 MICRONS RMS MAX.
 4. ALL DIMENSIONS PRIOR TO PLATING.
 5. EXCEED HALF THE SUM OF THEIR TOLERANCES.



S-D

(SHEET 1 OF 2)

M39012/28-0101

REVISIONS	
ISSUE	CHANGES
5	CN 16258A MJB 4 DEC 78
6	CN 22767 E JEP 16 NOV 81
7	CN 32302 A LNM 20 JUN 90

S-D

SCALE: 4:1
 USED ON: KA-19-19
 REF: _____
 PART: _____
 SPEC. KER 10004
 DATE: _____
 TNC BULKHEAD JACK
 DRAWN: MJB DATE: 4 DEC 78
 CHECKED: JEP DATE: 7 DEC 78
 KING ELECTRONICS
 48 HARBORLAND ROAD
 TUCKER, N. H. 03090
 M39012/28-0101
 (SHEET 1 OF 2)

ITEM	QTY	DESCRIPTION	PART NO.	REVISIONS
1	1	CLAMP NUT	704-7-MC7	5 CN 189384 40678
2	1	WASHER	89C-1-MC7	6 CN22767 E JEP 16 NOV. 81
3	1	GASKET	704-6-M99	7 CN 32302 A LNM 20 JUN 96
4	1	GASKET	492A-10-M99	
5	1	BRAID CLAMP	704-5-MC7	
6	1	LOCKWASHER	492A-12-MC7	
7	1	BUSHING	1-1451-1MC7	
8	1	HEX NUT	492A-9-MC7	
9	1	INSULATOR	1-1450-1M99	
10	1	INSULATOR	1-1453-1M99	
11	1	BNC CONTACT	1-1452-1M90	
12	1	BODY		
13	1	CABLING INSTRUCTIONS		

S-D

S-D

1. TOLERANCES: FRACTIONS & 2 PLACE DECIMALS ±.010 2. REMOVE ALL BURRS. BREAK SHARP EDGES .005 MAX.
 3 PLACE DECIMALS ±.004 ANGLES ±0°30' 3. NO FILLETS PERMITTED.
 T. I. R. CONCENTRICITY OF ANY 2 DIAMETERS MAY NOT 4. SURFACE ROUGHNESS 63 MICROINCHES RMS MAX.
 5. ALL DIMENSIONS BEING TO PLACING

UNLESS OTHERWISE SPECIFIED:

PARTS LIST

DRAWN	M M	DATE	5 DEC 78
APPR.	S	DATE	7 DEC 78

KINGS ELECTRONICS

40 MARBLEDALE ROAD
TUCKAHOE, N. Y. 10707M39012/28-0101
(SHEET 20F 2)