

SPECIFICATION OF RH SERIES

APPLICATIONS

The RH type bead cores are mainly produced for the cable wire assemblers and MATV CATV makers.

* Internal and external computer data and power cables


ORDERING CODE

K5B RH 14.2 x 28.5 x 6.35
(1) (2) (3) (4) (5)

- (1) MATERIAL
- (2) PRODUCT CODE
- (3) A DIM.
- (4) B DIM.
- (5) C DIM.



SHAPE



DIMENSIONS & CHARACTERISTICS

UNIT:mm

NO.	ORDERING CODE	A	B	C
1	RH 2.5x4x0.8	2.50±0.15	4.00±0.30	0.80±0.15
2	RH 2.5x7x0.8	2.50±0.15	7.00±0.30	0.80±0.15
3	RH 3x3x1	3.00±0.15	3.00±0.20	1.00±0.15
4	RH 3x3x1.2	3.00±0.15	3.00±0.20	1.20±0.15
5	RH 3x4x1	3.00±0.15	4.00±0.30	1.00±0.15
6	RH 3x6x1	3.00±0.15	6.00±0.30	1.00±0.15
7	RH 3.4x11.2x1.1	3.40±0.15	11.20±0.40	1.10±0.15
8	RH 3.5x3.5x0.8	3.50±0.15	3.50±0.20	0.80±0.15
9	RH 3.5x3.5x1.2	3.50±0.15	3.50±0.20	1.20±0.15
10	RH 3.5x3.5x1.7	3.50±0.15	3.50±0.20	1.70±0.15
11	RH 3.5x3.5x1.8	3.50±0.15	3.50±0.20	1.80±0.15
12	RH 3.5x4x1	3.50±0.15	4.00±0.30	1.00±0.15
13	RH 3.5x4x1.2	3.50±0.15	4.00±0.30	1.20±0.15
14	RH 3.5x4x1.3	3.50±0.15	4.00±0.30	1.30±0.15
15	RH 3.5x4x1.5	3.50±0.15	4.00±0.30	1.50±0.15
16	RH 3.5x4.5x0.8	3.50±0.15	4.50±0.30	0.80±0.15
17	RH 3.5x4.7x0.8	3.50±0.15	4.70±0.30	0.80±0.15
18	RH 3.5x5x0.8	3.50±0.15	5.00±0.30	0.80±0.15
19	RH 3.5x5x1.2	3.50±0.15	5.00±0.30	1.20±0.15
20	RH 3.5x5x1.3	3.50±0.15	5.00±0.30	1.30±0.15
21	RH 3.5x5x1.5	3.50±0.15	5.00±0.30	1.50±0.15
22	RH 3.5x5x1.8	3.50±0.15	5.00±0.30	1.80±0.15
23	RH 3.5x6x0.8	3.50±0.15	6.00±0.30	0.80±0.15
24	RH 3.5x6x1	3.50±0.15	6.00±0.30	1.00±0.15
25	RH 3.5x6x1.2	3.50±0.15	6.00±0.30	1.20±0.15

※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.

SPECIFICATION OF RH SERIES

NO.	ORDERING CODE	A	B	C
26	RH 3.5x6x1.3	3.50±0.15	6.00±0.30	1.30±0.15
27	RH 3.5x6x1.5	3.50±0.15	6.00±0.30	1.50±0.15
28	RH 3.5x6x1.8	3.50±0.15	6.00±0.30	1.80±0.15
29	RH 3.5x7x1.2	3.50±0.15	7.00±0.30	1.20±0.15
30	RH 3.5x7.5x0.8	3.50±0.15	7.50±0.30	0.80±0.15
31	RH 3.5x8x0.8	3.50±0.15	8.00±0.30	0.80±0.15
32	RH 3.5x8x1	3.50±0.15	8.00±0.30	1.00±0.15
33	RH 3.5x9x0.8	3.50±0.15	9.00±0.30	0.80±0.15
34	RH 3.5x9x1.3	3.50±0.15	9.00±0.30	1.30±0.15
35	RH 3.5x9.5x0.8	3.50±0.15	9.50±0.30	0.80±0.15
36	RH 3.5x14x0.8	3.50±0.15	14.00±0.40	0.80±0.15
37	RH 4x4x1.5	4.00±0.20	4.00±0.30	1.50±0.15
38	RH 4x4x2	4.00±0.20	4.00±0.30	2.00±0.15
39	RH 4x5x1.5	4.00±0.20	5.00±0.30	1.50±0.15
40	RH 4x5x2	4.00±0.20	5.00±0.30	2.00±0.15
41	RH 4x6x2	4.00±0.20	6.00±0.30	2.00±0.15
42	RH 4x7x2	4.00±0.20	7.00±0.30	2.00±0.15
43	RH 4x8x2	4.00±0.20	8.00±0.30	2.00±0.15
44	RH 4x10x1.5	4.00±0.20	10.00±0.40	1.50±0.15
45	RH 4x10x2	4.00±0.20	10.00±0.40	2.00±0.15
46	RH 4x12x2	4.00±0.20	12.00±0.40	2.00±0.15
47	RH 4x15x2	4.00±0.20	15.00±0.40	2.00±0.15
48	RH 4x17x2	4.00±0.20	17.00±0.40	2.00±0.15
49	RH 4.5x4.8x2.5	4.50±0.20	4.80±0.30	2.50±0.15
50	RH 4.5x7x2.5	4.50±0.20	7.00±0.30	2.50±0.15
51	RH 4.5x12x2.6	4.50±0.20	12.00±0.40	2.60±0.15
52	RH 4.6x11x2	4.60±0.20	11.00±0.40	2.00±0.15
53	RH 4.83x6.35x2.29	4.83±0.20	6.35±0.30	2.29±0.15
54	RH 5x5x2.3	5.00±0.20	5.00±0.30	2.30±0.15
55	RH 5x6.2x1.6	5.00±0.20	6.20±0.30	1.60±0.15
56	RH 5x6.35x2.36	5.00±0.20	6.35±0.30	2.36±0.15
57	RH 5x10x2.3	5.00±0.20	10.00±0.40	2.30±0.15
58	RH 5x11x1.5	5.00±0.20	11.00±0.40	1.50±0.15
59	RH 5x12x2.15	5.00±0.20	12.00±0.40	2.15±0.15
60	RH 5x18x2.15	5.00±0.20	18.00±0.40	2.15±0.15
61	RH 5x20x1.5	5.00±0.20	20.00±0.50	1.50±0.15
62	RH 5.7x8x1.5	5.70±0.20	8.00±0.30	1.50±0.15
63	RH 6x10x3	6.00±0.20	10.00±0.40	3.00±0.20
64	RH 6x10x4	6.00±0.20	10.00±0.40	4.00±0.20
65	RH 6x12.8x4	6.00±0.20	12.80±0.40	4.00±0.20
66	RH 6x18x3.15	6.00±0.20	18.00±0.40	3.15±0.20
67	RH 6x25x3	6.00±0.20	25.00±0.60	3.00±0.20
68	RH 6.35x12.7x3.3	6.35±0.20	12.70±0.40	3.30±0.20
69	RH 6.35x15.8x3.3	6.35±0.20	15.80±0.40	3.30±0.20
70	RH 6.5x10x4.3	6.50±0.20	10.00±0.40	4.30±0.20
71	RH 6.5x11x4.3	6.50±0.20	11.00±0.40	4.30±0.20
72	RH 7.5x7.5x2.4	7.50±0.20	7.50±0.30	2.40±0.15
73	RH 7.9x10x3	7.90±0.20	10.00±0.40	3.00±0.20
74	RH 7.9x12.8x4	7.90±0.20	12.80±0.40	4.00±0.20

※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



KING CORE ELECTRONICS INC.

Tel:886-3-4698855

Fax:886-3-4691395

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan

E-mail:kc@mail.kingcore.com.tw

Web Site:http://www.kingcore.com.tw

SPECIFICATION OF RH SERIES

NO.	ORDERING CODE	A	B	C
75	RH 7.9x19x3	7.90±0.20	19.00±0.40	3.00±0.20
76	RH 8x9x6	8.00±0.20	9.00±0.30	6.00±0.30
77	RH 8x9.8x6	8.00±0.20	9.80±0.30	6.00±0.30
78	RH 8x10x4	8.00±0.20	10.00±0.40	4.00±0.20
79	RH 8x10.06x3.18	8.00±0.20	10.06±0.40	3.18±0.20
80	RH 8x12x6	8.00±0.20	12.00±0.40	6.00±0.30
81	RH 8x16x5	8.00±0.20	16.00±0.40	5.00±0.25
82	RH 8x20x5	8.00±0.20	20.00±0.50	5.00±0.25
83	RH 9.3x9.5x4.5	9.30±0.30	9.50±0.30	4.50±0.20
84	RH 9.3x11x5.8	9.30±0.30	11.00±0.40	5.80±0.25
85	RH 9.5x9.5x4.8	9.50±0.30	9.50±0.30	4.80±0.20
86	RH 9.5x9.5x5.2	9.50±0.30	9.50±0.30	5.20±0.25
87	RH 9.5x10x5.2	9.50±0.30	10.00±0.40	5.20±0.25
88	RH 9.5x10x5.8	9.50±0.30	10.00±0.40	5.80±0.25
89	RH 9.5x10.4x5	9.50±0.30	10.40±0.40	5.00±0.25
90	RH 9.5x12.7x4.8	9.50±0.30	12.70±0.40	4.80±0.20
91	RH 9.5x14.5x5	9.50±0.30	14.50±0.40	5.00±0.25
92	RH 9.5x15.88x5	9.50±0.30	15.88±0.40	5.00±0.25
93	RH 9.5x16x5	9.50±0.30	16.00±0.40	5.00±0.25
94	RH 9.5x19x5	9.50±0.30	19.00±0.40	5.00±0.25
95	RH 9.5x19.5x5	9.50±0.30	19.50±0.40	5.00±0.25
96	RH 9.52x15.88x5.08	9.52±0.30	15.88±0.40	5.08±0.25
97	RH 9.8x11.4x0.8	9.80±0.30	11.40±0.40	0.80±0.15
98	RH 9.8x13.5x6.7	9.80±0.30	13.50±0.40	6.70±0.30
99	RH 9.8x19.05x6.7	9.80±0.30	19.05±0.40	6.70±0.30
100	RH 10x10x5	10.00±0.30	10.00±0.40	5.00±0.25
101	RH 10x10x6	10.00±0.30	10.00±0.40	6.00±0.30
102	RH 10x10x7	10.00±0.30	10.00±0.40	7.00±0.30
103	RH 10x14x6	10.00±0.30	14.00±0.40	6.00±0.30
104	RH 10.5x20x5.5	10.50±0.30	20.00±0.50	5.50±0.25
105	RH 10.5x25x5.5	10.50±0.30	25.00±0.60	5.50±0.25
106	RH 11x16x5	11.00±0.30	16.00±0.40	5.00±0.25
107	RH 11x18.5x5	11.00±0.30	18.50±0.40	5.00±0.25
108	RH 11x20x5	11.00±0.30	20.00±0.50	5.00±0.25
109	RH 11x25x5	11.00±0.30	25.00±0.60	5.00±0.25
110	RH 11.5x18.5x5	11.50±0.30	18.50±0.40	5.00±0.25
111	RH 11.5x20x4.3	11.50±0.30	20.00±0.50	4.30±0.20
112	RH 11.5x26x4.3	11.50±0.30	26.00±0.60	4.30±0.20
113	RH 11.8x15x7.3	11.80±0.30	15.00±0.40	7.30±0.30
114	RH 12x12x7	12.00±0.30	12.00±0.40	7.00±0.30
115	RH 12x12x8.5	12.00±0.30	12.00±0.40	8.50±0.30
116	RH 12x15x5.6	12.00±0.30	15.00±0.40	5.60±0.25
117	RH 12x15x7	12.00±0.30	15.00±0.40	7.00±0.30
118	RH 12x15x8.5	12.00±0.30	15.00±0.40	8.50±0.30
119	RH 12x20x5.6	12.00±0.30	20.00±0.50	5.60±0.25
120	RH 12x20x7.3	12.00±0.30	20.00±0.50	7.30±0.30
121	RH 12x30x5.6	12.00±0.30	30.00±0.70	5.60±0.25
122	RH 12.2x23x7.9	12.20±0.30	23.00±0.50	7.90±0.30
123	RH 12.3x20x7	12.30±0.30	20.00±0.50	7.00±0.30

※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



KING CORE ELECTRONICS INC.

Tel:886-3-4698855

Fax:886-3-4691395

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan

E-mail:kc@mail.kingcore.com.tw

Web Site:http://www.kingcore.com.tw

SPECIFICATION OF RH SERIES

NO.	ORDERING CODE	A	B	C
124	RH 12.32x25.4x4.88	12.32±0.30	25.40±0.60	4.88±0.20
125	RH 12.5x12.5x8	12.50±0.30	12.50±0.40	8.00±0.30
126	RH 12.5x15x5.2	12.50±0.30	15.00±0.40	5.20±0.25
127	RH 12.7x12.7x7.9	12.70±0.30	12.70±0.40	7.90±0.30
128	RH 14x15x9	14.00±0.40	15.00±0.40	9.00±0.30
129	RH 14.2x15x6.35	14.20±0.40	15.00±0.40	6.35±0.30
130	RH 14.2x15x7	14.20±0.40	15.00±0.40	7.00±0.30
131	RH 14.2x15x8	14.20±0.40	15.00±0.40	8.00±0.30
132	RH 14.2x18x6.35	14.20±0.40	18.00±0.40	6.35±0.30
133	RH 14.2x23.5x7	14.20±0.40	23.50±0.50	7.00±0.30
134	RH 14.2x28.5x6.35	14.20±0.40	28.50±0.60	6.35±0.30
135	RH 14.2x28.5x7	14.20±0.40	28.50±0.60	7.00±0.30
136	RH 14.2x28.5x8	14.20±0.40	28.50±0.60	8.00±0.30
137	RH 14.99x19x6.99	14.99±0.40	19.00±0.40	6.99±0.30
138	RH 14.99x27.94x6.99	14.99±0.40	27.94±0.60	6.99±0.30
139	RH 15.2x28.5x10.2	15.20±0.40	28.50±0.60	10.20±0.40
140	RH 15.25x17x9	15.25±0.40	17.00±0.40	9.00±0.30
141	RH 15.25x28x8	15.25±0.40	28.00±0.60	8.00±0.30
142	RH 15.65x28.57x6.99	15.65±0.40	28.57±0.60	6.99±0.30
143	RH 15.8x16x7.9	15.80±0.40	16.00±0.40	7.90±0.30
144	RH 15.88x28.57x7.87	15.88±0.40	28.57±0.60	7.87±0.30
145	RH 16x16x8	16.00±0.40	16.00±0.40	8.00±0.30
146	RH 16x17x9	16.00±0.40	17.00±0.40	9.00±0.30
147	RH 16x17.5x4.3	16.00±0.40	17.50±0.40	4.30±0.20
148	RH 16x20x7	16.00±0.40	20.00±0.50	7.00±0.30
149	RH 16x20x9	16.00±0.40	20.00±0.50	9.00±0.30
150	RH 16x28x7	16.00±0.40	28.00±0.60	7.00±0.30
151	RH 16x28x9	16.00±0.40	28.00±0.60	9.00±0.30
152	RH 16x28x10	16.00±0.40	28.00±0.60	10.00±0.40
153	RH 16x28.5x9	16.00±0.40	28.50±0.60	9.00±0.30
154	RH 17.07x25.4x8.76	17.07±0.40	25.40±0.60	8.76±0.30
155	RH 17.5x28.5x8	17.50±0.40	28.50±0.60	8.00±0.30
156	RH 17.5x28.5x8.3	17.50±0.40	28.50±0.60	8.30±0.30
157	RH 17.5x28.5x9.5	17.50±0.40	28.50±0.60	9.50±0.30
158	RH 17.5x28.5x10.7	17.50±0.40	28.50±0.60	10.70±0.40
159	RH 17.5x35x9.5	17.50±0.40	35.00±0.80	9.50±0.30
160	RH 18x18x10	18.00±0.50	18.00±0.40	10.00±0.40
161	RH 18x28x10	18.00±0.50	28.00±0.60	10.00±0.40
162	RH 18x29x10	18.00±0.50	29.00±0.60	10.00±0.40
163	RH 18.67x25x10.16	18.67±0.50	25.00±0.60	10.16±0.40
164	RH 18.67x28.57x10.16	18.67±0.50	28.57±0.60	10.16±0.40
165	RH 19x29x13	19.00±0.50	29.00±0.60	13.00±0.40
166	RH 19x31.5x5.8	19.00±0.50	31.50±0.70	5.80±0.25
167	RH 19x35x5.8	19.00±0.50	35.00±0.80	5.80±0.25
168	RH 19x35x6.3	19.00±0.50	35.00±0.80	6.30±0.30
169	RH 20x28.25x14.5	20.00±0.60	28.25±0.60	14.50±0.50
170	RH 25.91x28.57x12.83	25.91±0.60	28.57±0.60	12.83±0.40
171	RH 28x28x16	28.00±0.60	28.00±0.60	16.00±0.50
172	RH 28.5x28.57x13.77	28.50±0.60	28.57±0.60	13.77±0.40

※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



KING CORE ELECTRONICS INC.

Tel:886-3-4698855





















Fax:886-3-4691395

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan

E-mail:kc@mail.kingcore.com.tw

Web Site:http://www.kingcore.com.tw

SPECIFICATION OF RH SERIES



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



KING CORE ELECTRONICS INC.

Tel:886-3-4698855


Fax:886-3-4691395

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan

E-mail:kc@mail.kingcore.com.tw

Web Site:http://www.kingcore.com.tw

SPECIFICATION OF RH SERIES



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



KING CORE ELECTRONICS INC.

Tel: 886-3-4698855


Fax: 886-3-4691395

No. 269, Nanfong Rd., Pingjhen City, Taoyuan County, Taiwan

E-mail: kc@mail.kingcore.com.tw

Web Site: <http://www.kingcore.com.tw>

SPECIFICATION OF RH SERIES



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



KING CORE ELECTRONICS INC.

Tel:886-3-4698855





















Fax:886-3-4691395

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan

E-mail:kc@mail.kingcore.com.tw

Web Site:http://www.kingcore.com.tw

SPECIFICATION OF RH SERIES



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



KING CORE ELECTRONICS INC.

Tel:886-3-4698855


Fax:886-3-4691395

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan

E-mail:kc@mail.kingcore.com.tw

Web Site:http://www.kingcore.com.tw

SPECIFICATION OF RH SERIES



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



KING CORE ELECTRONICS INC.

Tel:886-3-4698855


Fax:886-3-4691395

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan

E-mail:kc@mail.kingcore.com.tw

Web Site:http://www.kingcore.com.tw

SPECIFICATION OF RH SERIES



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



KING CORE ELECTRONICS INC.

Tel: 886-3-4698855


Fax: 886-3-4691395

No. 269, Nanfong Rd., Pingjhen City, Taoyuan County, Taiwan

E-mail: kc@mail.kingcore.com.tw

Web Site: <http://www.kingcore.com.tw>

SPECIFICATION OF RH SERIES



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



KING CORE ELECTRONICS INC.

Tel:886-3-4698855





















Fax:886-3-4691395

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan

E-mail:kc@mail.kingcore.com.tw

Web Site:http://www.kingcore.com.tw

SPECIFICATION OF RH SERIES



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



KING CORE ELECTRONICS INC.

Tel:886-3-4698855


Fax:886-3-4691395

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan

E-mail:kc@mail.kingcore.com.tw

Web Site:http://www.kingcore.com.tw

SPECIFICATION OF RH SERIES



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



KING CORE ELECTRONICS INC.

Tel:886-3-4698855


Fax:886-3-4691395

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan

E-mail:kc@mail.kingcore.com.tw

Web Site:http://www.kingcore.com.tw

SPECIFICATION OF RH SERIES



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



KING CORE ELECTRONICS INC.

Tel:886-3-4698855





















Fax:886-3-4691395

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan

E-mail:kc@mail.kingcore.com.tw

Web Site:http://www.kingcore.com.tw

SPECIFICATION OF RH SERIES



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



KING CORE ELECTRONICS INC.

Tel:886-3-4698855


Fax:886-3-4691395

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan

E-mail:kc@mail.kingcore.com.tw

Web Site:http://www.kingcore.com.tw


SPECIFICATION OF RH SERIES



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.

SPECIFICATION OF RH SERIES



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only. King Core reserves the right to alter or revise the specifications without prior notification.



KING CORE ELECTRONICS INC.

Tel: 886-3-4698855









Fax: 886-3-4691395

E-mail: kc@mail.kingcore.com.tw

No. 269, Nanfong Rd., Pingjhen City, Taoyuan County, Taiwan

Web Site: <http://www.kingcore.com.tw>

SPECIFICATION OF RH SERIES



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



KING CORE ELECTRONICS INC.

Tel:886-3-4698855

Fax:886-3-4691395

E-mail:kc@mail.kingcore.com.tw

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan

Web Site:<http://www.kingcore.com.tw>