


CONFIGURATION		PART NUMBER	LENGTH
Cable Assembly, Molded, 14Awg, Standard Flex, Connectors - Male Straight Entry/ Female Straight Entry		P29008-MXX	TBD
DIMENSIONS			
 WIRING DIAGRAM BLACK 14AWG WHITE 14AWG RFD 14AWG GREEN 14AWG FACE VIEW FACE VIEW			
TECHNICAL DATA			
TEMPERATURE RANGE:	-40C to +125C		
PROTECTION:	IP 67, NEMA 6P		
VOLTAGE RATING:	600VAC/600VDC		
BODY:	OIL RESISTANT PVC		
CONTACTS:	COPPER ALLOY		
CONTACT PLATING:	5 INCHES (MINI) GOLD, OVER 25 INCHES (MINI) NICKEL		
CONNECTOR FACE:	PVC		
AMPERAGE:	15AMP		
CABLE TYPE:	14 AWG, 600 V, TC-ER/STOOW		
COUPLER:	MACHINED ALUMINUM, ANODIZED		
CABLE DIAMETER:	.62" (15.75mm) NOMINAL		
APPROVALS:	UL, CSA		