

PRODUCT FINDER

- Large Cabinet Racks
- Communications
Cabinets/Racks
- Cabinets
- Open Racks
- Server Racks
- Aluminum Enclosures and
Chassis
- Small Metal Enclosures
- Die Cast Boxes
- Plastic Enclosures
- NEMA Boxes
(Water-tight Plastic
and Fiberglass)
- NEMA Boxes
(Water-tight Sheet Metal)
- NEMA Boxes
(Water-tight Aluminum)
- Accessories
- Brackets
- Custom Enclosures

NEMA Boxes

NEMA 4X - PIP



Click on Image for Larger View

These High impact resistance Gray Polycarbonate (PC) resin 10% glass fiber filled molded enclosures rated IP67 (TUV) and meet NEMA 1, 2, 4, 4x type 6 specifications. UV stabilized UL94-V0 flammability rating suggested service temperature -40C to 120C. and are ideal for PCB enclosures, junction boxes and other applications in the electrical and electronic industries. Available in a variety of sizes.

Follow BUD On:

in

t

YouTube

g+

rss

Design Features

- Body Made of Gray Polycarbonate (PC) resin 10% glass fiber filled
- Cover made of Gray Polycarbonate (PC)
- High impact resistance
- IP-67 TUV rating to keep out dust and water in extreme conditions.
- UL508 / NEMA type 4X and type 6 listed #E343339.
- RoHs compliant
- UL industrial controls & CE Low Voltage directive 2006/95/EC listed
- Non-chlorinated & non-brominated flame retardant With UL-94 V0 rating.
- Suitable for outdoor use with respect to exposure to Ultraviolet Light, Water Exposure and Immersion in accordance with UL 746C.
- Nonmetallic captive screws without the risk of stripping.
- Good chemical resistance
- Continuous gasket

BUD - Cat# Grey Cover	BUD -Cat# Clear cover	Drawings	L (in)	W (in)	D (in)	Weight (lb.)	Accessories	
							Internal steel panel#	External mounting bracket#
PIP-11760	PIP-11760-C	PDF DXF	5.118	3.15	1.378	0.11	PIX-11760	Stainless Steel mounting bracket for PIP NBX10922
PIP-11763	PIP-11763-C	PDF DXF	5.118	3.15	3.346	0.13	PIX-11760	
PIP-11766	PIP-11766-C	PDF DXF	5.118	5.118	1.378	0.13	PIX-11766	
PIP-11767	PIP-11767-C		5.118	5.118	2.362	0.14	PIX-11766	

		PDF DXF						Plastic mounting bracket for PIP
PIP-11772	PIP-11772-C	PDF DXF	7.087	7.087	2.953	0.19	PIX-11772	
PIP-11774	PIP-11774-C	PDF DXF	7.087	7.087	4.921	0.22	PIX-11772	
PIP-11775	PIP-11775-C	PDF DXF	10.039	7.087	2.953	0.23	PIX-11775	
PIP-11777	PIP-11777-C	PDF DXF	10.039	7.087	4.921	0.25	PIX-11775	

[DXF](#) Autocad DXF Specifications File

[PDF](#) Adobe PDF Specifications File

(Right Click and save link to your computer. Requires CAD software such as AutoCAD)

[!\[\]\(a870788d6ed9b8fd294b7654a8c8526b_img.jpg\) Download PDF Viewer](#)

For the majority of our enclosures we offer 3D STEP files upon request

SEARCH PRODUCTS BY SIZE AND TYPE

Try Our Product Selector Tool.

BEGIN SEARCHING >

