




- 1. FOR ADDITIONAL SPECIFICATIONS SEE AMP PRODUCT SPEC 108-7519.
- 2. SWITCH SHOWN IN OPEN POSITION.
- 3. ALL CHARACTERS AND ROCKERS ARE WHITE, HOUSING IS BLACK.
- 4. HOT MELT STRIPPABLE TRANSPARENT SEAL, SEE FIG 1.
- 5. 8.00 [.315] DIMENSION APPLIES AT TERMINAL TIPS. TERMINALS ARE $7.62 - 0.00$ $^{+0.25}_{+.010}$ [.300 - .000] AT MOUNTING SURFACE
- 6. SPECIAL PACKAGING IN 22 INCH TUBES.
- 7. UV CURED STRIPPABLE SEAL, SEE FIG 1.
- 8. ALL MATERIALS AND FINISHES SHALL COMPLY WITH EU DIRECTIVE 2002/95/EC OF 27 JAN 2003 (ROHS)
- 9. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

8	N/A	22.3 [.88]	8	6-382758-8
8	N/A	14.7 [.58]	5	6-382758-5
8	4	12.2 [.48]	4	5-382758-4
9	SUPERCEDED	N/A	8	1-382758-8
9	SUPERCEDED	N/A	5	1-382758-5
	SUPERCEDED	7	8	382758-8
	4	12.2 [.48]	4	382758-4
SEAL		DIM A	NO OF POSN	TYCO PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R.TALLEY 03MAR93	Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: mm [INCHES]		CHK C.WHITT 04MAR93		
		APVD J.SIDDEN 04MAR93		
		PRODUCT SPEC		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	SWITCH ASSY, DIP, TYPE C, 7000 SERIES, SPST, SIDE ACTUATED	
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.13 [.005] 4 PLC ± - ANGLES ± -		—	SIZE A2	CAGE CODE 00779
MATERIAL: HOUSING & ROCKERS: POLYESTER CONTACTS: BERYLLIUM COPPER		WEIGHT —	DRAWING NO C=382758	RESTRICTED TO —
FINISH: CONTACTS: PLATED 0.00076 [.000030] MIN GOLD IN CONTACT AREA OVER 0.00127 [.000050] MIN. NICKEL.		CUSTOMER DRAWING	SCALE 4:1	SHEET 1 OF 1 REV D2