

9885

Max. 15 W

AC/DC DESKTOP REGULATED

- Max. 15 W output power
- Universal input voltage
- 3-pin IEC 320 mains connector
- UL approved
- Compliance with relevant worldwide safety standards
- Exchangeable output plugs, providing:
 - reduced stocking requirements
 - short delivery lead times
 - snap-locks for added safety



Technical specifications

Input voltage:	90 - 264 VAC.
Max. output power:	15 W.
Load regulation:	± 5%
Line regulation:	± 0.5% maximum at full load.
Switch frequency:	47-63 kHz.
Inrush current:	<30 A (230 VAC) at 25°C cold start.
Hold up time:	> 5 ms.
Temperature range	
* Operating:	-0°C to +70°C.
* Storage:	-40°C to +85°C.
Derating:	Derated from 100% at +40°C linearly to 50% at +70°C.
Ripple:	1% p-p max..
Efficiency:	> 70% at max. load.
Current limiting:	Yes.
Overvoltage protection:	Yes.
Electrical safety standards:	EN 60950, UL 1950
EMC standards:	
* Emission:	EN 61000-6-3
* Immunity:	EN 61000-6-1
Reliability:	MTBF > 100.000 h at nominal load at 25°C ambient..
Mains connection:	3-pin IEC 320.
Output terminals:	Secondary cable w/exch. Plug
Dimensions (LxWxH):	91 x 38 x 36 mm (without plug).
Weight:	165 g

Some technical specifications may differ for other models and voltage versions.

Survey of voltage versions

Output voltage (VDC) ±5%	Load current (A)	Output power (W)
5	2,4	12
9	1,6	14,4
12	1,25	15
24	0,625	15

07032006

www.mascot.no
sales@mascot.no

Phone:
Fax:

Main Office
PO Box 177
N-1601 FREDRIKSTAD
NORWAY
+47 69 36 43 00
+47 69 36 43 01

Mascot UK
PO Box 1560, Andover
SP11 8QZ HAMPSHIRE
UK
+44 (0)1264 357177
+44 (0)1264 364055

Mascot DE-AT-CH-BENELUX
Hirschbergstr. 28/7
D-74838 LIMBACH
GERMANY
+49 6287 95140
+49 6287 95141

Mascot DE-AT-CH-BENELUX
Tettmanger Str. 52
D-88239 WANGEN
GERMANY
+49 7528 951677
+49 7528 951678

Mascot France
38 rue Leo Lagrange
94270 Le Kremlin Bicêtre
FRANCE
+33 1 46 58 71 85
+33 1 46 58 71 85