




LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
		R		REV PER ECO-15-016062	09NOV15	KG



- THIS RCPT. IS DESIGNED TO CONFORM TO THE LATEST ISSUE OF MIL-C-24308
- MAX WIRE INSUL TO BE USED WITH THIS RCPT IS .054 DIA
- METAL RETENTION CLIPS ARE INCLUDED IN INSERTS
- PACKAGE STAMPED M 24308/2-291F
- THIS RCPT. WILL ACCEPT SIZE 22 SOCKET CONTACT M 39029/57-354 OR ANY AMP HDD-22 SOCKET CONTACT

- AMP PART NO. STAMPED ON CONNECTOR REPRESENTS KIT NUMBER WITH CONTACTS
- UL/CSA DESIGNATION STAMPED IN THIS AREA,OPTIONAL

SUPSD BY 204510-1	STEEL, CLASS G	PHENOLIC COLOR: BLACK	204510-3
SUPSD BY 206065-4	BRASS	DIALLYL PATHALATE COLOR: BLUE	204510-2
	STEEL, CLASS G	DIALLYL PATHALATE COLOR: BLUE	204510-1
	SHELL MAT'L	INSERT MAT'L	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS CHK F.C.BALLEW III APVD D.J.M.	12-2-87 1-25-88 1-26-88	TE Connectivity	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0 PLC ± -		PRODUCT SPEC	
		1 PLC ± -		APPLICATION SPEC	
MATERIAL SEE TABLE		FINISH SEE CALLOUTS		WEIGHT -	
				SIZE A1	
				CAGE CODE 00779	
				DRAWING NO 204510	
				RESTRICTED TO -	
				SCALE 4:1	
				SHEET 1 OF 1	
				REV R	