





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		AM2	REVISED PER ECO-11-004587	11MAR11	RK	HMR



1. FOR ADDITIONAL SPECIFICATIONS SEE AMP PRODUCT SPEC 108-7532.
 2. SWITCH SHOWN IN OPEN POSITION.
 3. ALL CHARACTERS AND ROCKERS ARE WHITE, HOUSING IS BLUE.
 4. STAMPING WILL VARY ON 2 AND 3 POSITION SIDES DUE TO SPACE RESTRICTIONS.
- 5 .315 DIMENSION APPLIES AT TERMINAL TIPS.
TERMINALS ARE .300^{+.010}_{-.000} AT MOUNTING SURFACE.
- 6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

	△6	OBSOLETE	FIG 7	————	.58	5	8-435668-7
		OBSOLETE	FIG 6		1.08		8-435668-6
		OBSOLETE	FIG 5		1.28	12	8-435668-5
SUPERSEDED BY 2-435668-5		FIG 3 & 4		FIG 1		6	8-435668-3
	OBSOLETE		FIG 2		.48	4	8-435668-0
	△6	OBSOLETE			.58	5	3-435668-5
					.48	4	3-435668-4
					.38	3	3-435668-3
					1.28	12	3-435668-2
					1.18	11	3-435668-1
					1.08	10	3-435668-0
					.98	9	2-435668-9
					.88	8	2-435668-8
					.78	7	2-435668-7
					.28	2	2-435668-6
.68	6	2-435668-5					
SUPERSEDED BY 3-435668-2					1.28	12	1-435668-1
	OBSOLETE				————	1.08	10
			————	.98	9	435668-8	
			————	.88	8	435668-7	
SUPERSEDED BY 2-435668-7			————	.78	7	435668-6	
			————	.68	6	435668-5	
			————	.58	5	435668-4	
			————	.48	4	435668-3	
SUPERSEDED BY 3-435668-3			————	.38	3	435668-2	
	△6	OBSOLETE		————	.28	2	435668-1
			MARKING	SEALING TAPE	A	NO OF POSN	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	02JAN90	TE Connectivity			
		CHK	03JAN90				
		APVD	03JAN90	NAME			
		PRODUCT SPEC					
		APPLICATION SPEC		SWITCH ASSY, DIP, TYPE C, 7100 SERIES, SPST, LOW PROFILE			
MATERIAL		FINISH	WEIGHT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
HOUSING & ROCKERS: POLYESTER CONTACTS: COPPER ALLOY		CONTACTS: PLATED .000030 MIN GOLD IN CONTACT AREA OVER .000050 MIN NICKEL	—	A2	00779	C=435668	—
CUSTOMER DRAWING				SCALE	4:1	SHEET	1 of 2
				REV			
				AM2			

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		-	SEE SHEET 1	-	-	-




FIG 2




FIG 5




FIG 3




FIG 6




FIG 4




FIG 7

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R.TALLEY 02JAN90		 TE Connectivity			
		CHK R.MILLER 03JAN90					
DIMENSIONS: INCHES		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		APVD H.LEITER 03JAN90		NAME	
		0 PLC ± -		PRODUCT SPEC		SWITCH ASSY, DIP, TYPE C, 7100 SERIES, SPST, LOW PROFILE —	
		1 PLC ± -		—			
		2 PLC ± -					
		3 PLC ± .005		APPLICATION SPEC			
		4 PLC ± -		—			
MATERIAL		FINISH		WEIGHT —		RESTRICTED TO —	
				A2 00779 C=435668			
CUSTOMER DRAWING				SCALE 4:1		SHEET 2 of 2	
						REV. AM2	