








ASSMANN
WSW Components

MiniDIN-Steckverbinder, ungeschirmt und vollgeschirmt
MiniDIN-connector, unshielded and fully shielded






Isolierkörper PBT, UL94V-0	Insulator PBT, UL94V-0
Kontakte Messing, Verzinnt	Contacts Brass, tin plated
Strombelastbarkeit 2A DC	Current rating 2A DC
Nennspannung 12V DC	Current voltage 12V DC
Kontaktwiderstand 100mΩ max	Contact resistance 100mΩ max.
Betriebstemperatur -25°C - +85°C	Operating temperature -25°C - +85°C

ohne Schirmung/no shield



Ansicht von unten/bottom view

Vollgeschirmt, 5 Seiten/full shielded, 5 sides



Bestellcode : A - DIO - x / x
Ordercode :

Bitte „x“ durch die unten geeignete Option ersetzen
Please replace „x“ with appropriate option listed below

1. 2.

1. Ausführung
M -Buchse, ohne Schirmung
FS -Buchse, Vollgeschirmt 5 Seiten

Version
M -Socket, no shield
FS -Socket, full shielded 5 sides

2. Polzahl
03, 04, 05, 06, 07, 08

No. of contacts
03, 04, 05, 06, 07, 08