



REVISONS			
LOC	DIST		
—	—	P	L/R
		J2	PER ECR-14-009692
DESCRIPTION	DATE	DMN	APD
	25SEP2014	JL	JL



CONNECTION TABLE			
CABLE	CONN.A	CONN.B	
UNIT	WIRE COLOR	PIN	PIN
A (BROWN)	GREEN	1	1
	DRAIN WIRE	2	2
	WHITE	3	3
A (GREEN)	GREEN	4	4
	DRAIN WIRE	5	5
	WHITE	6	6
A (BLUE)	GREEN	7	7
	DRAIN WIRE	8	8
	WHITE	9	9
A (RED)	GREEN	10	10
	DRAIN WIRE	11	11
	WHITE	12	12
C	RED	13	13
	VIOLET	14	14
C	WHITE	15	15
	GRAY	16	16
B	YELLOW	17	17
	ORANGE	18	18
	PINK	19	19
SHIELD BRAID		SHELL	SHELL



A-A VIEW

- UNIT A:
- P1: WHITE-GREEN
 - P2: WHITE-GREEN
 - P3: WHITE-GREEN
 - P4: WHITE-GREEN
- UNIT B:
- P5: YELLOW-ORANGE
- UNIT C:
- 7. VIOLET
 - 8. WHITE
 - 9. GRAY
 - 10. PINK

0.003 LB	SOLDER BAR	1770019-8	5000±50
0.003 LB	SOLDER WIRE	1770019-7	1500±20
2	PC SHELL FOR HDMI	1770019-6	1000±20
0.25 MR	TAPE/VINYL, COLOR: BLACK,W:12.5MM, L:50MM	1770019-5	750±10
0.1 MR	HEAT SHRINK TUBING, ID: 0.7MM, BLACK	1770019-4	500±10
0.018 KG	PVC, 40P, COLOR: BLACK	1770019-3	250±10
0.07 MR	HEAT SHRINK TUBING, ID: 1.5MM, BLACK	1770019-2	3000±30
2	HDMI 19PIN PLUG, CONTACT: 30U" GOLD, INSULATION: BLACK, SHELL: NICKEL PLATED	1770019-1	2000±20
AR	UL20276 (1P*30AWG+DRAIN+AL/MYLAR)*4+30AWG*1P +28AWG*5C+AL/MYLAR+DRAIN+BRAID, COLOR: BLACK		
QTY	U/M	DESCRIPTION	ITEM NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.			
DMN	S.WU	18AUG2013	
CHK	S.CHEN	18AUG2013	
APD	W.KODAMA	18AUG2013	
NAME			
C/A,HDMI TO HDMI			
SIZE			
A3 00779 C=1770019			
QTY			
1			

DIMENSIONS:	
mm	
0 P/C	±
1 P/C	±
2 P/C	±
3 P/C	±
4 P/C	±
ANGLES	±

TOLERANCES UNLESS OTHERWISE SPECIFIED:	
±	±
±	±
±	±
±	±
±	±

FINISH	
-	

MATERIAL	
-	

WEIGHT	
6.96KG	

CUSTOMER DRAWING	
-	

SCALE	
1:1	
SHEET	
1 OF 3	
REV	
J2	

LOC		DIST		REVISIONS			
—		—		P	LIR	DESCRIPTION	DATE
—		—		—	—	SEE SHEET 1	—

NOTES:

PACKING MATERIAL MET TE SPEC TEC-138-702.

* CADMIUM AND CADMIUM COMPOUNDS CONTENT:

5 PPM UNDER (PLASTIC,RUBBER,INK,PIGMENT,PAINT)

* LEAD,CADMIUM,CHROM VI AND MERCURY IN PACKAGING

MATERIALS CONTENT: 100 PPM (COMBINED) UNDER.

1. MATERIAL:

1.1 BAG: POLYSTYRENES

1.2 BOX: CORRUGATED FIBERBOARD

1.3 CLAPBOARD: CORRUGATED FIBERBOARD






2. DIMENSION:

2.1 BAG: L=318, W=229


△ 2.2 BOX: L=335, W=300, H=300

△ 2.3 BOX: L=350, W=299, H=146





△ 2.4 BOX: L=540, W=345, H=240



△ 13.2KG	233.3g	60	1	60	1770019-8
△ 5.77KG	85.4g	50	1	50	1770019-7
△ 4.72KG	64.3g	50	1	50	1770019-6
△ 8.94KG	148.8g	50	1	50	1770019-2
△ 7.89KG	106.5g	60	1	60	1770019-1
GROSS WEIGHT	NET WEIGHT	PCS/BAG	BAG/BOX	PCS/BOX	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.									
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DMN		S.WU		18AUG2013	
mm		0 P/C ±		APD		W.KODAMA		18AUG2013	
		1 P/C ±		PRODUCT SPEC		NAME		C/A,HDMI TO HDMI	
		2 P/C ±		APPLICATION SPEC				-	
		3 P/C ±						-	
		4 P/C ±						-	
		ANGLES ±						-	
		FINISH ±						-	
MATERIAL		-		WEIGHT		6.96KG		A3	
				CUSTOMER DRAWING				00779	
								C=1770019	
				SCALE		1:1		SHEET	
								2 of 3	
								REV J2	
								RESTRICTED TO	

LOC		DIST		REVISIONS			
				P	LIR	DESCRIPTION	DATE
						SEE SHEET 1	



38.1±2

25.4±2

MADE IN CHINA

- NOTES:
- PACKING MATERIAL MET TE SPEC TEC-138-702.
- * CADMIUM AND CADMIUM COMPOUNDS CONTENT:
 - 5 PPM UNDER (PLASTIC,RUBBER,INK,PIGMENT,PAINT)
 - * LEAD,CADMIUM,CHROM VI AND MERCURY IN PACKAGING MATERIALS CONTENT: 100 PPM (COMBINED) UNDER.
1. MATERIAL:
- 1.1 BAG: POLYSTYRENES
 - 1.2 BOX: CORRUGATED FIBERBOARD
 - 1.3 CLAPBOARD: CORRUGATED FIBERBOARD
2. DIMENSION:
- 2.1 BAG: L=318, W=229
 - 2.2 BOX: L=335, W=300, H=300
 - 2.3 BOX: L=350, W=299, H=146
 - 2.4 BOX: L=540, W=345, H=240

THIS DRAWING IS A CONTROLLED DOCUMENT.									
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:							
mm		0 P/C	±	1 P/C	±	2 P/C	±	3 P/C	±
		4 P/C	±	ANGLES ±					
MATERIAL		FINISH		-					
-		-		-					
CUSTOMER DRAWING		CUSTOMER DRAWING							
WEIGHT		6.96KG							
APPLICATION SPEC		-							
-		-							
SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO			
A3		00779		C=1770019		-			
SCALE		1:1		SHEET		3 OF 3		REV J2	