


**Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.**



ORIENTATION



1. SUPPLIED WITH SILVER PLATED
HEX NUT AND LOCKWASHER.
2. TUSONIX STANDARD PART NUMBER: 4201-000.
TUSONIX RoHS COMPLIANT PART NUMBER: 4201-000 LF.
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
3. LEAD FINISH: STANDARD PART #: 60/40 SOLDER PLATED. RoHS PART #: SILVER PLATED.
4. PART MARKING: TRADEMARK AND VARIATION NUMBER ON HEX FLATS.
STANDARD PART: BLACK INK. RoHS PART: GREEN INK.

MIN. CAP. (pF)	WORKING VOLTAGE (WVdc)		CURRENT (Idc)	I.R. MIN.	DWV	MINIMUM NO LOAD INSERTION LOSS (dB) AT 25°C PER MIL-STD -220			
						10 MHz	100 MHz	1 GHz	10 GHz
1500	85°C	125 °C	10 A	10 G	400 VDC 2 SEC.				
	200	100				5	45	65	70

[illegible]