


# 2.5mm Stereo Plug

171-0025



2.5mm Stereo Plug



Dimensions: mm (In)

## SPECIFICATIONS

|                               |                     |
|-------------------------------|---------------------|
| <b>Breakdown Voltage:</b>     | 500VAc for 1 Minute |
| <b>Insulation Resistance:</b> | 100MΩ min. @ 500VDC |
| <b>Contact Resistance:</b>    | 50mΩ max.           |
| <b>Tolerance:</b>             | ±0.5                |
| <b>Max Wire O.D.</b>          | 3.8mm               |

## MATERIALS

| No. | Part Name | Material | Finish |
|-----|-----------|----------|--------|
| 1   | Contact A | Brass    | Ni     |
| 2   | Contact B | Brass    | Ni     |
| 3   | Contact C | Brass    | Ni     |
| 4   | Metal     | Brass    | Ni     |
| 5   | Insulator | POM      | - - -  |
| 6   | Terminal  | Brass    | Ni     |
| 7   | Cap       | PE       | - - -  |

Date Last Revised: 6-28-05

Available from Mouser Electronics  
1-800-346-6873  
www.mouser.com

KC-300544

171-0025

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[171-0025](#)