





Dimensions: mm (In.)






Terminal



.250" Sq.



Function



Electrical Specifications:

- Rating: 16A/125VAC, 1/3HP; 10A/250VAC, 1/2HP
- Contact resistance: 50mΩ max.
- Insulation resistance: 500VDC 100MΩ min.
- Dielectric strength: 1500VAC for 1 min.

Note:

- RoHS Compliant

Cut-out

X	Y	X	Y
0.75~3	27.6-0.1	13.8+0.1	
3~4	27.8-0.1	13.8+0.1	
4~5	28.0-0.1	13.8+0.1	

Mouser Stock No.	Button	Function
103-R13-238A-01W-EV	White	A
103-R13-238A-01B-EV	Black	A
103-R13-238C-01W-EV	White	C
103-R13-238C-01B-EV	Black	C
103-R13-238D-01W-EV	White	D
103-R13-238D-01B-EV	Black	D

Illuminated Rocker Switches

103-R13-238A-01W-EV, 103-R13-238A-01B-EV, 103-R13-238C-01W-EV,
103-R13-238C-01B-EV, 103-R13-238D-01W-EV, 103-R13-238D-01B-EV

Mountain Switch

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mountain Switch:

[103-R13-238D-01B-EV](#) [103-R13-238C-01B-EV](#) [103-R13-238D-01W-EV](#) [103-R13-238A-01W-EV](#) [103-R13-238A-01B-EV](#) [103-R13-238C-01W-EV](#)