



- Buzzer in combination with Xenon Flash
- Integrated mounting bracket
- Optical and audible signal can be triggered separately
- Continuous or pulse tone adjustable
- High protection rating IP 65

TECHNICAL SPECIFICATIONS:

Dimensions (Diameter x Height):	91 mm x 120 mm
Housing:	PC/ABS-Blend; PC grey
Dome:	PC, transparent
Connection:	Screwable connection with wire protection max. 1.5 mm ²
Cable entry:	Membrane cover up to Ø 9 mm
Current consumption Flash + Buzzer:	<150 mA at 24 V; < 40 mA at 115 V; < 60 mA at 230 V
Tone type:	Continuous tone or pulse tone, adjustable
Tone frequency:	2.3 kHz
Flash energy:	1 Ws
Flash frequency:	1 Hz
Sound output:	90 dB
Fixing:	Bracket mounting
Life duration:	4 x 10 ⁶ flashes

ORDER SPECIFICATIONS:

	24 V ≐	115 V ~	230 V ~
red	423 110 75	423 110 67	423 110 68
yellow	423 310 75	423 310 67	423 310 68

Available from May 2005

