




WIRE CONNECTION

P1	WIRE COLOR	P2
6		15
7		12
8		14
14,16		9
15		5,10
C1		1
KEY		6
C2		2
KEY		7
C3		3
KEY		8
C4		13
SHELL	BRAID SHIELDS	SHELL

Materials:

- Cable: 30AWG(7/0.102)COAXIALx3C+28AWG(7/0.127)x5C+
+28AWG(7/0.127)*1Pair+AL/MY+Drain Wire+Braid Shields+
Jacket: PVC OD:7.0±0.15MM
Color: Black
- Connector: P1: DVI 29P: 24P+4+Key Digital/Analog Gold Flash (Contact: Nickel Plated Shell)
P2: HDB 15P Male Gold Flash (Contact: Nickel Plated Shell)
- Shield: P1&P2 Copper Foil 360° soldered to connector shell & cable shielding
- Hood: P1&P2: Molded Type, PVC 45P, Color: Black

Electrical:

- 100% Short Open & Mis Wire Test
- Contact Resistance 3Ω Max
- Insulation Resistance 10MΩ Min
- Hi-Pot Voltage 300V DC

⊗ = Assmann Logo

RoHS
Compliant

ITEM NO

AK622N-5-R

TITLE

DVI-D/A <=> VGA HDB15 Cable, 5 Meters

ASSMANN
Electronics, Inc.

1840 W. Drake Drive, Suite 101 - Tempe, AZ 85283

Toll Free: 1-877-277-6266 Email: info@usa-assmann.com

THIS DRAWING IS UNPUBLISHED

© Copyright 2009 by Assmann Electronic Components
All International Rights Reserved