

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

46819-0011

Status:


Active

Overview:

EXTreme Guardian™ System

Description:

EXTreme Guardian™ High Power Terminal, 10 AWG Crimp, 0.76µm Gold (Au)



Documents:

Drawing (PDF)

Product Specification PS-46819-001 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Terminals
Series	46819
Application	Power
Crimp Quality Equipment	Yes
Overview	EXTreme Guardian™ System
Product Name	EXTreme Guardian™
UPC	883906730932
Physical	
Gender	Female
Material - Metal	Copper
Material - Plating Mating	Nickel
Material - Plating Termination	Gold
Net Weight	3.400/g
Packaging Type	Reel
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	4.70mm max.
Wire Size AWG	10
Wire Size mm²	N/A
Material Info	
Reference - Drawing Numbers	
Product Specification	PS-46819-001
Sales Drawing	SD-46819-001

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

46819Series

Mates With

46817 Housing

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Mini-Mac™ Applicator Air Feed for Power 60 Amp Crimp Terminals, 10 AWG	0638320800

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION