



Product Data Sheet


Part No. PT-1507 Washable Reflow Type (SMD)

PT-1507



14.8 × 14.8 × 6.8

DIMENSIONS



Type	Unit	PT-1507
Color		Black
Rated Voltage	(V)	12
Operating Voltage	(V)	1~20
Current Consumption	(mA)	< or = 31
Capacitance at 120 Hz	(pF)	15000±30%
Sound Output (Min)	(dB)	> or = 85
Resonance Frequency	(Hz)	5000±500
Operating Temp	(C)	-20~+70
Storage Temp	(C)	-30~+80
Weight	(g)	2
Dimension	mm	14.8 x 14.8 x 6.8
*Value applying at rated voltage		
*distance for measurement 10cm		

FREQUENCY RESPONSE

