


Flexible Coaxial Cable Assembly

RG 142 SMA straight plug / SMA right angle plug

308-0315-xxxxA



List Nomenclature

- | | |
|-----------------------------------|-------------------|
| 1. SMA straight plug connector | A01077 |
| 2. SMA right angle plug connector | A01097 |
| 3. Black Protective Sleeve | A20007 |
| 4. Coaxial Cable | A91051 (RG142B/U) |

Electrical Specifications

Impedance	:	50 ± 2 Ohms
Operating Frequency	:	DC to 8 GHz
Velocity of Propagation	:	70%
Voltage Withstand	:	1500 Veff

Insertions Losses

Frequency (MHz)	500	1500	3000	6000	8000
Insertions Losses max (dB/m)	0,48	0,73	1,06	1,65	1,97

Mechanical Specifications

Inner Conductor	Solid	Ø = 0,94 mm (0,04 inches)
Dielectric	PTFE	Ø = 2,95 mm (0,12 inches)
Braid 1	CuAg	Ø = 3,54 mm (0,14 inches)
Braid 2	CuAg	Ø = 4,10 mm (0,16 inches)
Jacket	FEP	Ø = 4,95 mm (0,19 inches)

Environmental Specifications

Operating Temperature Range	:	-55°C à +150°C
-----------------------------	---	----------------

Conditions of delivery

Mechanical check	:	Length
Electrical test	:	Continuity / Rigidity