


COMMON MODE EMI SUPPRESSION INDUCTORS



-  Low profile or vertical mounting available
-  Windings balanced within one percent
-  For use in switching power supply input filter circuits
-  Dielectric strength 1250 V_{RMS}
-  Designed with 3.0 mm minimum creep distance between windings


Electrical Specifications @ 25°C— Operating Temperature -40° to +130° C

Low Profile Part Number	Vertical Mount Part Number	Rated RMS Current ¹ (Amps)	Load VA ² at RMS Line		Inductance at 1 kHz (mH MIN)	Test Level Volts RMS 1.0 kHz	Leakage Inductance 130 kHz (μH MIN)	DCR Max. each WDG (Ω)	Package Number	Lead Diameter Inches ± .003	
			117 V	220 V						Low Profile	Vertical Mount
PE-62891	PE-62911	1.8	210	420	10.0	0.50	130	0.240	1	0.032	0.032
PE-62892	PE-62912	3.5	400	800	3.0	0.20	35	0.060	1	0.032	0.032
PE-62893	PE-62913	6.0	700	1400	1.0	0.08	12	0.020	1	0.036	0.036
PE-62894	PE-62914	2.6	300	600	16.0	1.00	180	0.160	2	0.032	0.040
PE-62895	PE-62915	3.2	375	750	8.0	0.50	90	0.120	2	0.032	0.040
PE-62896	PE-62916	5.2	600	1200	4.0	0.20	45	0.040	2	0.036	0.036
PE-62897	PE-62917	7.5	875	1750	2.0	0.08	25	0.020	2	0.047	0.047

NOTES: 1. Rated RMS current for 40°C rise at any input voltage. 2. **Caution** — do not exceed rated RMS current ratings.

Mechanicals

Vertical Package




Package Number	A	B	C	D	E	F	G
1	1.15 29,21	.550 13,97	.400 10,15	.800 20,32	.45 11,43	.015 0,38	1.15 29,21
2	1.44 36,57	.800 20,32	.600 15,24	.900 22,86	.70 17,78	.030 0,76	1.50 38,10

Unless otherwise specified, all tolerances are ± .010
0,25

Dimensions: Inches
mm

Low Profile Package



Package Number	A	B	C	D	E
1	1.25 31,75	.600 15,24	1.00 25,40	.015 0,38	.900 22,86
2	1.50 38,10	.800 20,32	1.28 32,51	.010 0,25	1.083 27,50

Schematic



For More Information :

UNITED STATES (Worldwide)

12220 World Trade Drive
San Diego, CA 92128
U.S.A.
<http://www.pulseeng.com>
TEL: 858 674 8100
FAX: 858 674 8262

UNITED KINGDOM (Northern Europe)

1 & 2 Huxley Road
The Surrey Research Park
Guildford, Surrey GU2 5RE
United Kingdom
TEL: 44 1483 401700
FAX: 44 1483 401701

FRANCE (Southern Europe)

Zone Industrielle
F-39270
Orgelet
France
TEL: 33 3 84 35 04 04
FAX: 33 3 84 25 46 41

SINGAPORE (Southern Asia)

150 Kampong Ampat
#07-01/02
KA Centre
Singapore 368324
TEL: 65 6287 8998
FAX: 65 6280 0080

TAIWAN, R.O.C. (Northern Asia)

3F-4, No. 81, Sec. 1
HsinTai Wu Road
Hsi-Chih, Taipei Hsien
Taiwan, R.O.C.
Tel: 886 2 2698 0228
FAX: 886 2 2698 0948

HONG KONG (China/Hong Kong)

9/F, Phase 2, Tai Sang
Shatin Warehouse Centre
6 Wong Chuk Yeung Street
Fotan, Shatin, Hong Kong
TEL: 852 2788 6588
FAX: 852 2776 1055

DISTRIBUTOR

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners.