







PC card drilling dimensions(after plating) _____
(thickness 1.60±0.20mm)



rev	ecn no	dr	date
C	-	JOU	1996/09/09
D	LS05-001	MPE	2005/03/09
E	LS05-0056	MPE	2005/06/27
F	LS06-0097	LGO	2006/07/29
G	I09-0268	NG	2009-11-24
H	I10-0059	NG	2010-02-23
-	-	-	-

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C01-8646-0000

www.fciconnect.com

Dr	JOUBERT	1994-09-23	ANGULAR	0.X	±0.1	size	A3	Scale	2
Eng	PESSON	1994-09-23	LINEAR	0.XX	±0.1	ECN	I10-0059		
Chr	NIRMAL GEORGE	2010-02-23	0.XX' ±2°	0.XXX	±0.1				
Appr	SUDHIR VARMA	2010-02-23	Product family			D-SUB	Spec ref	-	

MALE CONNECTEUR DELTA D S

straight solder type for

tolerance std

ISO 1302

ISO 406 ISO 1101

projection

mm

Scale

2

CUSTOMER

sheet 1 of 1

TIN LEAD PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.79	10.96	D09P24A*GL00
15	39.14	33.32	25.18	25.12	19.18	D15P24A*GL00
25	53.03	47.04	39.12	38.84	33.12	D25P24A*GL00
37	69.32	63.50	55.68	55.30	49.68	D37P24A*GL00

Protection: 4 --> flash AU
6 --> 0.76µ AU

LEAD FREE PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.79	10.96	D09P24A*GL00LF
15	39.14	33.32	25.18	25.12	19.18	D15P24A*GL00LF
25	53.03	47.04	39.12	38.84	33.12	D25P24A*GL00LF
37	69.32	63.50	55.68	55.30	49.68	D37P24A*GL00LF

Protection: 4 --> flash AU
6 --> 0.76µ AU

