



**Wiha Quality Tools**  
Germany


Go To  
Image Index

Go To  
Numerical Index

22

Toll Free: (800) 494-6104

## Wiha TORX® Protorn Screwdrivers



Through hardened for optimum wear resistance

Molded on ergonomic handle proportioned to blade sizes

High performance tool steel

Black finish blades



### 455 91 Set 6 Pcs. TORX®

| Item No. | Size   | mm    | Size   | mm      | lbs. |
|----------|--------|-------|--------|---------|------|
| 455 91   | 455 06 | T7 50 | 455 21 | T10 80  | .72  |
|          | 455 11 | T8 60 | 455 26 | T15 80  |      |
|          | 455 16 | T9 60 | 455 31 | T20 100 |      |

### 455 92 Set 8 Pcs. TORX®

| Item No. | Size   | mm     | Size   | mm      | lbs. |
|----------|--------|--------|--------|---------|------|
| 455 92   | 455 11 | T8 60  | 455 31 | T20 100 | 1.07 |
|          | 455 16 | T9 60  | 455 36 | T25 100 |      |
|          | 455 21 | T10 80 | 455 41 | T27 115 |      |
|          | 455 26 | T15 80 | 455 46 | T30 115 |      |



### 455 89 Set 15 Pcs. TORX®

| Item No. | Size   | mm      | Size   | mm      | lbs. |
|----------|--------|---------|--------|---------|------|
| 455 89   | 455 05 | T6 50   | 455 31 | T20 100 | 2.2  |
|          | 455 06 | T7 50   | 455 36 | T25 100 |      |
|          | 455 11 | T8 60   | 455 41 | T27 115 |      |
|          | 455 16 | T9 60   | 455 46 | T30 115 |      |
|          | 455 21 | T10 80  | 455 51 | T40 130 |      |
|          | 455 22 | T10 275 | 455 56 | T45 130 |      |
|          | 455 26 | T15 80  | 455 61 | T50 130 |      |
|          | 455 28 | T15 275 |        |         |      |



### 484 00 1/4" Bit Holding Screwdriver, With Wiha-Protorn Handle

Magnetic, holds bit and screw. Retainer out of stainless steel. Shaft CVM steel, nickel-plated. Handle, molded on, impact resistant.

| Item No. | Size | mm  | Inch | mm  | Inch | lbs. | pcs. |
|----------|------|-----|------|-----|------|------|------|
| 484 00   | 1/4  | 125 | 5.0  | 243 | 9.6  | .24  | 10   |



### 455 TORX® Screwdriver, With Wiha-Protorn Handle

Blade high alloy CVM steel, hardened, black finish. Molded on ergonomic Wiha-Protorn handle, impact resistant.

| Item No. | Size | mm  | Inch | mm  | Inch | mm  | Inch | lbs. | pkg. |
|----------|------|-----|------|-----|------|-----|------|------|------|
| 455 05   | T6   | 50  | 2.0  | 3.5 | .139 | 129 | 5.1  | .05  | 10   |
| 455 06   | T7   | 50  | 2.0  | 3.5 | .139 | 129 | 5.1  | .05  | 10   |
| 455 11   | T8   | 60  | 2.4  | 3.5 | .139 | 139 | 5.5  | .06  | 10   |
| 455 16   | T9   | 60  | 2.4  | 4.0 | .157 | 149 | 5.8  | .08  | 10   |
| 455 21   | T10  | 80  | 3.1  | 4.0 | .157 | 170 | 6.7  | .10  | 10   |
| 455 22   | T10  | 275 | 10.8 | 4.0 | .157 | 363 | 14.2 | .13  | 10   |
| 455 26   | T15  | 80  | 3.1  | 4.0 | .157 | 170 | 6.7  | .10  | 10   |
| 455 28   | T15  | 275 | 10.8 | 4.0 | .157 | 373 | 14.6 | .15  | 10   |
| 455 31   | T20  | 100 | 3.9  | 4.0 | .157 | 190 | 7.5  | .11  | 10   |
| 455 36   | T25  | 100 | 3.9  | 4.5 | .177 | 190 | 7.5  | .11  | 10   |
| 455 41   | T27  | 115 | 4.5  | 5.5 | .216 | 215 | 8.4  | .11  | 10   |
| 455 46   | T30  | 115 | 4.5  | 6.0 | .236 | 215 | 8.4  | .20  | 10   |
| 455 51   | T40  | 130 | 5.1  | 7.0 | .275 | 240 | 9.4  | .28  | 10   |
| 455 56   | T45  | 130 | 5.1  | 8.0 | .315 | 240 | 9.4  | .27  | 10   |
| 455 61   | T50  | 130 | 5.1  | 9.0 | .354 | 240 | 9.4  | .31  | 10   |

PREVIOUS

NEXT