



Dimensions: mm (in.)

P.C. Mounting

POS.1	POS.2	POS.3
(ON)	OFF	(ON)
2-3	OPEN	2-1

Switch Function**Electrical Specifications:**

- Rating: 0.4VA Max./20V AC or DC Max.
- Contact Resistance: 20mΩ max. initial @ 2-4VDC 100mA
- Insulation Resistance: 1,000MΩ min.
- Dielectric Strength: 1,000 V RMS@sea level

Mechanical Specifications:

- Mechanical Life: 50,000 make-and-break cycles
- Operating Temperature: -30°C to 85°C

Note:

- RoHS Compliant by Exemption

Soldering Process:

- Wave Soldering: Recommended soldering temperature: 260±5°C
Duration of solder immersion: 5±1 sec.
(PCB is 1.6mm in thickness)

Sealed Sub-Miniature Toggle Switch
108-2BS4T2Z52-EVX

Mountain
Switch

Available from Mouser Electronics

www.mouser.com

1-800-346-6873

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[108-2BS4T2Z52-EVX](#)