

ATW019


Tubular screw terminal block, centerline 10 mm / 0.394 inches, flat base, horizontal wire entry

Technical Data

V / A / AWG	300 / 30 / 22 - 12 solid / 14 - 10 stranded
V / A / AWG Screw torque	400 / 20 / 18 - 14 max. 4.4 lbs.-in
2.5 mm ² Screw torque	400 V / 24 A max. 0.5 Nm
Wire strip length	7.3 mm / 0.287 in.
Pole size	1 to 12
Color	Natural

Dimensions in mm

1 mm = 0.0394 in.



	A	B	C	D	E	F
mm	117.0	20.2	15.8	10.0	3.6	3.2±0.1
inches	4.606	0.795	0.622	0.394	0.142	0.126

L = (PS-1)10+7.0 mm

Part numbers (P/N)

(information: page 165)

Complete the part number by adding the pole size.

ATW019

centerline 10 mm / 0.394 inches

P/N ATW019

	01	02	03	04	05	06	07	08
	09	10	11	12				

Standard pole sizes

Available on demand. Minimum order quantity 5000 pieces per item.

ATW029


Tubular screw terminal block, centerline 10 mm / 0.394 inches, flat base, horizontal wire entry, wire protector

Technical Data

V / A / AWG	300 / 30 / 22 - 12 solid / stranded / 10 solid
V / A / AWG Screw torque	400 / 20 / 18 - 14 max. 4.4 lbs.-in
2.5 mm ² Screw torque	400 V / 24 A max. 0.5 Nm
Wire strip length	7.3 mm / 0.287 in.
Pole size	1 to 12
Color	Natural

Dimensions in mm

1 mm = 0.0394 in.



	A	B	C	D	E	F
mm	117.0	20.2	15.8	10.0	3.6	3.2±0.1
inches	4.606	0.795	0.622	0.394	0.142	0.126

L = (PS-1)10+7.0 mm

Part numbers (P/N)

(information: page 165)

Complete the part number by adding the pole size.

ATW029

centerline 8 mm / 0.394 inches

P/N ATW029

	01	02	03	04	05	06	07	08
	09	10	11	12				

Standard pole sizes

Available on demand. Minimum order quantity 5000 pieces per item.