

# Accessories - Drilling - Metal Drilling - EXTREME DEWALT® Cobalt Bits



The standard DEWALT range satisfies the application needs of the professional end user, but EXTREME 2 METAL drill bits offer outstanding drilling speed as well as a hole quality that is second to none. EXTREME COBALT bits are also available in order to offer users drilling into stainless steel the same performance advantages.

Catalog Number	M.O.Q.	Length	Diameter	Working Length	Pack Quantity
DT5403	1	49mm	2mm	24mm	2
DT5404	1	57mm	2.5mm	30mm	2
DT5405	1	61mm	3mm	33mm	2
DT5408	1	70mm	3.5mm	39mm	2
DT5409	1	75mm	4mm	43mm	2
DT5412	1	80mm	4.5mm	47mm	1
DT5414	1	86mm	5mm	52mm	1
DT5415	1	93mm	5.5mm	57mm	1
DT5416	1	93mm	6mm	57mm	1
DT5417	1	101mm	6.5mm	63mm	1
DT5418	1	109mm	7mm	69mm	1
DT5419	1	117mm	8mm	75mm	1
DT5421	1	125mm	9mm	81mm	1
DT5422	1	133mm	10mm	87mm	1
DT5424	1	142mm	11mm	94mm	1
DT5426	1	151mm	12mm	101mm	1
DT5427	1	151mm	13mm	101mm	1



## Features

- Precision ground twist drill bit manufactured to DIN 338 with distinct heat and wear resistance properties. Right hand cutting helix, type N flute.
- 5% cobalt alloyed High Speed Steel for stability at high temperatures when drilling tough materials.
- Unique tip improves efficiency and eliminates walking.
- Finish - Gold Ferrous