



DH SERIES

GENERAL PURPOSE FILTERS



INTRODUCTIONS

DE & DH Series filters are for UL 544 & UL 2601 health care equipment.

COMPONENTS

PART NO.	Cx (uF)	L (mH)
06DHEG3H	0.015	0.55
06DHEG3V		
06DHAG5		

MINIMUM INSERTION LOSS IN dB

COMMON MODE (L-G) IN 50 OHM SYSTEM							
TYPE	CURRENT RATING	FREQUENCY-MHz					
		0.15	0.15	0.15	0.15	0.15	0.15
06DHEG3H	6A	12	15	20	22	20	15
06DHEG3V	6A	12	15	18	20	20	18
06DHAG5	6A	10	15	18	20	20	18

MECHANICAL CONSTRUCTION



EG3H



EG3V





AG5

SPECIFICATIONS

- Maximum leakage current each line-to-ground: @ 115VAC 60Hz: 2uA
@ 250VAC 50Hz: 5uA
- Hipot rating (one minute)
line-to-ground: 2250VDC
line-to-line: 1450VDC
- Operating frequency: 50/60Hz
- Rated voltage: 115/250VAC

ELECTRICAL SCHEMATIC



UNIT: INCH
mm