



FEATURES:

- ✓ Converts BNC (female) cables / connectors to miniature banana plugs for test versatility.
- ✓ Miniature banana plug springs are gold plated Beryllium Copper for excellent electrical connection.
- ✓ BNC connector is molded directly to the wire for pull strength durability and dust and moisture resistance.
- ✓ Black wire is connected to BNC shell, red wire to BNC center contact.
- ✓ Miniature banana plugs are stackable.

MATERIALS:

BNC: Nickel Plated Brass, Center Contact: Gold Plated Brass

Dielectric: PTFE

Wire: 20 AWG, PVC Insulated

Miniature Banana Plug: Body: Brass Gold Plated, Spring: Beryllium Copper, Gold Plated

Insulation: Polypropylene, color matches color of wire.

RATINGS:

Operating Voltage: Hands free testing in controlled voltage environments: 500 VRMS Max.

Operating Temperature: +131°F (+55°C) Max.

ORDERING INFORMATION: Model 4815*

* Custom lengths are available, contact Pomona Product Support at: 1-800-241-2060

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

4815