




PANDUIT PART NO. *	BUNDLE DIA.		A	B	C	D	E	F	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	TIP STYLE	WEIGHT lbs./100 pcs. (g)
	MIN. in (mm)	MAX. in (mm)										
PLT4S	.06 (1.5)	4.00 (102)	.052 (1.3)	.190 (4.8)	.265 (6.7)	.220 (5.6)	.337 (8.6)	14.5 (368)	50 (222)	STANDARD	CURVED	.56 (254)
PLT4.5S	.06 (1.5)	4.50 (114)	.052 (1.3)	.190 (4.8)	.265 (6.7)	.220 (5.6)	.337 (8.6)	15.5 (394)	50 (222)	STANDARD	CURVED	.57 (257)
PLT5S	.06 (1.5)	5.00 (127)	.052 (1.3)	.190 (4.8)	.265 (6.7)	.220 (5.6)	.337 (8.6)	17.5 (445)	50 (222)	STANDARD	CURVED	.65 (293)
PLT6LH	.188 (4.8)	6.00 (152)	.075 (1.9)	.300 (7.6)	.350 (8.8)	.330 (8.4)	.480 (12.2)	21.9 (556)	120 (534)	LIGHT HEAVY	STRAIGHT	1.86 (845)
PLT7LH	.188 (4.8)	7.00 (178)	.075 (1.9)	.300 (7.6)	.350 (8.8)	.330 (8.4)	.480 (12.2)	24.7 (627)	120 (534)	LIGHT HEAVY	STRAIGHT	2.09 (950)
PLT8LH	.188 (4.8)	8.00 (203)	.075 (1.9)	.300 (7.6)	.350 (8.8)	.330 (8.4)	.480 (12.2)	27.6 (701)	120 (534)	LIGHT HEAVY	STRAIGHT	2.32 (1054)
PLT9LH	.188 (4.8)	9.00 (229)	.075 (1.9)	.300 (7.6)	.350 (8.8)	.330 (8.4)	.480 (12.2)	30.5 (775)	120 (534)	LIGHT HEAVY	STRAIGHT	2.56 (1161)
PLT10LH	.188 (4.8)	10.31 (262)	.075 (1.9)	.300 (7.6)	.350 (8.8)	.330 (8.4)	.480 (12.2)	34.3 (871)	120 (534)	LIGHT HEAVY	STRAIGHT	2.83 (1285)

NOTES:

- 1) RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC.
 *2) SEE www.panduit.com FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, PART MATERIAL, & PART COLOR.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

						TITLE PAN-TY CABLE TIES - PLT SERIES			
						CUSTOMER DRAWING			
						ITEM REVISION NAME W10001CC/26			
						DATASET FILE NAME W10001CC/26-SS-5540 SHEET 3 CUSTOMER			
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm) .X = - - - .XXX = .020 (.51) .XX = .02 (.51) ANGLES = - - -			
						THIRD ANGLE PROJECTION			
						DRAWING NUMBER: SS-5540 SHEET 3			
						DRAWN BY CEW			
						DATE 12-27-84			
						CHK HVP			
						SCALE NONE			
						SHT 1 OF 1			
						SIZE A			

26	8/13/13	BWG	KJM	RTFI	UPDATED TITLE BORDER.	SS-5540/26
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

DI01000A/16