

AVR Series 550VA Ultra-compact Line-Interactive 120V UPS with USB port

MODEL NUMBER: **AVR550U**



Highlights

- 550VA ultra-compact 120V line interactive UPS
- Corrects brownouts and overvoltages from 83V to 147V
- 4 battery supported outlets, 4 surge-only outlets
- USB port, TEL/DSL protection, Wall mountable, 98% efficient
- NEMA 5-15P input plug and 8 NEMA 5-15R outlets

Package Includes

- AVR550U UPS System
- USB cable
- Instruction manual

Description

Tripp Lite's AVR550U Ultra-Compact Line Interactive UPS offers complete power protection for desktop PCs, network workstations and a wide variety of professional and consumer electronic devices. Uninterruptible Power Supply / UPS circuits switch to battery backup mode within milliseconds to keep connected equipment running without interruption or data loss during power failures. Automatic Voltage Regulation / AVR power conditioning maintains smooth, continuous operation of connected equipment during brownouts and overvoltages. Surge-only outlets offer convenient protection for printers and other desktop accessories not requiring battery support. AC and dataline surge suppression prevents connected equipment damage. USB communications port supports built-in power management and auto-shutdown features of Windows and Mac OS X or full featured monitoring and data-saving auto-shutdown options using Tripp Lite's free PowerAlert monitoring software.

Features

- AVR550U ultra-compact 120V line interactive UPS offers complete AC power protection from blackouts, brownouts and transient surges
- 550VA / 300 watt UPS output capacity
- Uninterruptible Power Supply / UPS operation maintains battery-derived AC output during blackouts to prevent data loss and system downtime for connected equipment
- Built-in USB port enables data-saving unattended shutdown when used with Tripp Lite's PowerAlert software, available via FREE download from www.tripplite.com
- HID-compliant USB port also enables integration with built-in power management and auto shutdown features of Windows and Mac OS X
- Automatic Voltage Regulation / AVR corrects extended brownouts and overvoltages from 83 to 147V, without using battery power
- 3.2 minutes runtime at 100% load (300 watts), 10.2 minutes runtime at 50% load (150 watts)
- 20 minutes runtime for a desktop computer system consuming 80 watts continuous
- 8 built-in NEMA 5-15R outlets, two with extra wide spacing to accommodate transformer plugs
- 4 UPS battery backup outlets, plus 4 additional surge-only outlets
- Right angle NEMA 5-15P input connection with 6ft / 1.8m line cord
- Network grade AC surge and lightning protection is available from all outlets; Built-in data line surge suppression protects a single dialup or DSL line
- Supports Tripp Lite's Watchdog system service to restore operation to locked equipment through soft reboot of application/OS or hard power off/on reboot of connected equipment, ideal for unattended kiosk applications



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- 98% line mode efficiency rating uses less energy and BTU emissions
- Built-in grounding lug
- Hot swappable user battery replacement
- Space saving, ultra-compact housing with support for wall-mount, desktop or floor placement

Specifications

OUTPUT	
Output Volt Amp Capacity (VA)	550
Output Watt Capacity (watts)	300
Nominal Output Voltage(s) Supported	115V; 120V
Frequency compatibility	60 Hz
Output voltage regulation (line mode)	120V (+8%, -21%)
Output voltage regulation (Battery mode)	115V (+/- 5%)
Built-in UPS output receptacles	8 5-15R outlet(s)
Surge suppression only outlets	4 UPS outlets, 4 surge-only outlets
Output AC waveform (AC mode)	Sine wave
Output AC waveform (battery mode)	PWM sine wave
INPUT	
Rated input current (at maximum load)	12A
Nominal Input Voltage(s) Supported	120V AC
UPS input connection type	5-15P
UPS Input cord length (ft.)	6
UPS Input cord length (m)	1.8
Recommended Electrical Service	15A 120V
Phase	Single-Phase
BATTERY	
Full load runtime (minutes)	3.2 min. (300w)
Half load runtime (minutes)	10.2 min. (150w)
DC system voltage (VDC)	12
Battery recharge rate (included batteries)	9 hours (10% to 90%)
Battery Access	Battery access door



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Battery replacement description	Hot-swappable, user replaceable batteries
VOLTAGE REGULATION	
Voltage regulation description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 83 to 147
Overvoltage correction	Input voltages between 128 and 147 are reduced by 12%
Undervoltage correction	Input voltages between 83 and 104 are boosted by 14%
LEDS ALARMS & SWITCHES	
LED Indicators	2 LEDs indicate power status and overload/check battery status
Alarms	Audible alarm indicates power-failure and overload status
Switches	Combination switch controls on/off power status and self-test operation
SURGE / NOISE SUPPRESSION	
UPS AC suppression joule rating	420
UPS AC suppression response time	Instantaneous
UPS Dataline suppression	1 line TEL/DSL (1 in / 1 out)
EMI / RFI AC noise suppression	Yes
PHYSICAL	
Installation form factors supported with included accessories	Tower; Ultra-compact desktop
Primary form factor	Desktop
UPS / Power Module dimensions in primary form factor (height x width x depth / inches)	3.5 x 11.2 x 6
UPS / Power Module dimensions in primary form factor (height x width x depth / cm)	8.9 x 28.6 x 15.2
UPS / Power Module weight (lbs)	11
UPS / Power Module weight (kg)	5
UPS Shipping dimensions (height x width x depth / inches)	4.8 x 13.5 x 8.8
UPS Shipping dimensions (height x width x depth / cm)	12.1 x 34.3 x 22.2
Shipping weight (lbs)	12
Shipping weight (kg)	5.5
UPS housing material	ABS
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC mode BTU / hr. (full load)	54
AC mode efficiency rating (100% load)	95%
COMMUNICATIONS	
Communications interface	USB (HID enabled)
PowerAlert software	Free download from www.tripplite.com
Communications cable	USB interface cable included
WatchDog compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
Network UPS Tools Compatibility	Yes
LINE / BATTERY TRANSFER	
Transfer time	4 milliseconds
Low voltage transfer to battery power (setpoint)	83
High voltage transfer to battery power (setpoint)	147
SPECIAL FEATURES	
Cold Start (startup in battery mode during a power failure)	Cold-start operation supported
High availability UPS features	Hot swappable batteries
Green & high efficiency features	Greater than 95% efficiency - GREEN UPS
CERTIFICATIONS	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category B (EMI)
WARRANTY	
Product Warranty Period (U.S. & Canada)	3-year limited warranty
Product Warranty Period (Latin America)	3-year limited warranty
Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	3-year limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$100,000 Ultimate Lifetime Insurance
---	---

Related Items

Optional Products

Model Number	Description	Qty.
CT120	Instant-Read- AC Outlet Circuit Tester	1
DCATV	Network Surge Suppressor - Essential protection for TV/VCR coaxial lines	1
DNET1	Network Surge Suppressor - Essential protection for data and communication lines	1
DTEL2	Network Surge Suppressor - Essential protection for data and communication lines	1
U005-10I	10-inch USB A/A Gold Extension Cable (USB-A Right Angle Male to USB-A Female)	1
U222-004-R	4-Port USB2.0 Ultra-Mini Hub	1
WATCHDOGSW	WatchDog Service Monitoring / Reboot Software	1
WEXT5-INTERNET	5-Year Extended Warranty - For Internet Office, AVR and ECO Series UPS Systems	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at:
<http://www.tripplite.com/sku/AVR550U>.

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement.
Specifications are subject to change without notice. Photos may differ slightly from final products.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[AVR550U](#)