

13 Series


RoHS
Compliant

NYLON 6.6

GENERAL PURPOSE

MATERIAL OPERATING TEMPERATURE: -40°C to +85°C

APPLICATION OPERATING TEMPERATURE: -10°C to +85°C



Part Number	Ball Diameter mm [Inch]	Length mm [Inch]	Max Bundle Diameter mm [Inch]
HEAD TYPE A			
13-100	2.5 [.095]	100 [4.0]	25.0 [0.98]
HEAD TYPE B			
13-150	2.5 [.095]	150 [6.0]	36.0 [1.41]
13-200	2.5 [.095]	200 [8.0]	51.9 [2.04]

PART NUMBER SYSTEM

13 - 200 B - C

SERIES

LENGTH

MATERIAL/COLOR


N: Natural
B: Normal UV Black

PACKAGE SIZE

C: 100PCS
Number: Other Quantity

HEAD TYPE A

HEAD TYPE B



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Qualtek:

[13-100B-C](#) [13-100N-C](#) [13-150B-C](#) [13-150N-C](#) [13-200B-C](#) [13-200N-C](#)