


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
DF	S0		D	REV PER ECO-05-002584	07-05	AA	DE

1. MARKED PER MIL-STD-130; .09 HIGH CHARS.
2. TO MATE WITH AMP LGH-1/2 RECEPTACLE WITH .53 [13.4] BARREL DEPTH.
3. OPERATING VOLTAGE: 10 KVDC AT 0 TO 70,000 FEET, -55°C TO 125°C.
- △4 PIGTAIL IS SOLDER DIPPED. (868399-1,-2, & -3 ONLY)
- △5 TOLERANCE OF LEAD LENGTH:
UP TO 24 INCHES [609.6] = ±.12 [±3.0]
24 INCHES [609.6] & UP = ±1%
- △6 INSULATION CUT BUT NOT REMOVED. (5-868399-3 ONLY)



△6	15.00 [381.0]	5-868399-3
△4	15.00 [381.0]	868399-3
△4	36.00 [914.4]	868399-2
△4	24.00 [609.6]	868399-1
REMARKS	A DIM △5	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	30-JUL-90	tyco Electronics Tyco Electronics Corporation Harrisburg, Pa 17105-3608		
		CHK	28-AUG90			
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD	28-AUG-90	NAME LEAD ASSY POS STOP, SGL END (RED) LGH-1/2		
		PRODUCT SPEC				
	FINISH	APPLICATION SPEC		SIZE	CAGE CODE	DRAWING NO
MATERIAL SEE CALLOUTS	SEE CALLOUTS	WEIGHT	-	A2	00779	C=868399
CUSTOMER DRAWING				SCALE	2:1	SHEET 1 OF 1
						REV D