






PANDUIT PART NO.	BUNDLE DIA MIN - MAX.	DIMENSIONS				MATERIAL	COLOR	WEIGHT grams 100 pcs
		'A'	'B'	'C'	'D'			
HCME06A12-...20	6 - 12	1.2	15	12.0	9.7	NYLON 6/6	BLACK	150
HCME06A12-..130	6 - 12	1.2	15	12.0	9.7	ACETAL		



Application
Specification
Detail View
(See note 3)



SCALE: FULL

NOTES:

1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, AND COLOR.
2. (*) DIMENSIONAL VARIANCE IS POSSIBLE DUE TO MOLDING PROCESS RELATED SINK MARKS.
3. APPLICATION SPECIFICATION:
PUNCHED RECTANGULAR HOLE: 4.0 x 11.0 mm
PANEL THICKNESS: 0.6 - 1.2 mm

CAD FILENAME/LAYERS

G01932BF_PB_HCME06A12_07

PANDUIT CORP.

TINLEY PARK, ILLINOIS

HARNESS CLIP FOR EDGE MOUNT

Unless otherwise specified, all dimensions are metric tolerance: $\pm 0.5\text{mm}$

DRAWN BY JAD

MAT'L:

SCALE 2X

DATE 5-7-98

SEE TABLE

DRAWING NO.

GB1932BF

DWG
SIZE
A

7	3-3-06	TMSA		REVISED OVERALL HEIGHT DIMENSION WAS 18.8 NOW IS 18.3	GB1932BF	7				
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP		