




LOC		DIST		REVISIONS					
—		—		P	LTR	DESCRIPTION	DATE	DWN	APVD
					L	REV PER ECO-15-016062	10NOV15	KG	CD



- THIS RCPT. IS DESIGNED TO CONFORM TO THE LATEST ISSUE OF MIL-C-24308
 - MAX WIRE INSUL TO BE USED WITH THIS RCPT IS .068 DIA
 - STAINLESS STEEL RETENTION CLIPS ARE INCLUDED IN INSERTS
 - PACKAGE STAMPED M24308/2-293F
 - THIS RCPT. WILL ACCEPT SIZE 20 SOCKET CONTACT M24308/10 OR AMP # 205090
- AMP PART NO. INK STAMPED ON CONNECTOR REPRESENTS KIT NUMBER WITH CONTACTS
- UL/CSA DESIGNATION STAMPED IN THIS AREA.

OBSOLETE	BRASS	205417-2
	STEEL PER ASTM-A-109	205417-1
	SHELL MAT'L	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 12-9-87	TE Connectivity	
DIMENSIONS: INCHES		CHK F.C. BALLEW III 12-10-87		
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD -	NAME	
	0 PLC ± -	PRODUCT SPEC	AMPLIMITE RCPT FOR SOCKET CONTACTS HI-DENSITY HDM-20 CONNECTOR, SIZE 2 (15 POS) SERIES 109 W/FLOAT BUSHINGS	
	1 PLC ± -	APPLICATION SPEC		
	2 PLC ± -	WEIGHT -		
MATERIAL SEE CALLOUTS		SIZE 20	CAGE CODE 00779	DRAWING NO 205417
		RESTRICTED TO		
		CUSTOMER DRAWING	SCALE 4:1	SHEET 1 OF 1 REV L