






嵌合図
MATED DRAWING

Rev. G 2012/01/11




2CKTS

3CKTS


4CKTS

5CKTS


6CKTS



7CKTS



9CKTS




10CKTS

REVISED	EC NO: JTR2016-0015 G DRWN:KAGAI 02 2016/03/01 CHKD:HKOMATSU 2016/03/04 APPR:YAMAMOTO 2016/03/08	DESCRIPTION	QUALITY SYMBOLS F₀=0 F₁=0 F₂=0 F₃=0	GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH		DIMENSION STYLE MM ONLY		SCALE 4:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION					
				4 PLACES ± --- ± ---		DRAWN BY SHSHIBATA	DATE 2009/02/18	TITLE 2.0MM PITCH W/B CONN. WAFER ASSY ST. SMT molex							
				3 PLACES ± --- ± ---		CHECKED BY HKOMATSU	DATE 2009/02/18								
				2 PLACES ± --- ± ---		APPROVED BY AKANESHI GE	DATE 2009/02/18								
				1 PLACE ± --- ± ---		MATERIAL NO.		DOCUMENT NO. SD-560020-001 SHEET NO. 2 OF 4							
				0 PLACE ± --- ± ---		SEE CHART									
				ANGULAR ± °											
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

	10		9		8		7		6		5		4		3		2		1		
F	Sn NATURAL	11.8	29.1	33.7	36.6	560020-1520		15	Au NATURAL	11.8	29.1	33.7	36.6	560020-1530		15	F				
		11.8	27.1	31.7	34.6	560020-1420		14		11.8	27.1	31.7	34.6	560020-1430		14					
		11.8	25.1	29.7	32.6	560020-1320		13		11.8	25.1	29.7	32.6	560020-1330		13					
		11.8	23.1	27.7	30.6	560020-1220		12		11.8	23.1	27.7	30.6	560020-1230		12					
		11.8	21.1	25.7	28.6	560020-1120		11		11.8	21.1	25.7	28.6	560020-1130		11					
		11.8	19.1	23.7	26.6	560020-1020		10		11.8	19.1	23.7	26.6	560020-1030		10					
		11.8	17.1	21.7	24.6	560020-0920		9		11.8	17.1	21.7	24.6	560020-0930		9					
		11.8	15.1	19.7	22.6	560020-0800/-0820		8		11.8	15.1	19.7	22.6	560020-0830		8					
		11.8	13.1	17.7	20.6	560020-0700/-0720		7		11.8	13.1	17.7	20.6	560020-0730		7					
		11.8	12	15.7	18.6	560020-0600/-0620		6		11.8	12	15.7	18.6	560020-0630		6					
		9.8	10	13.7	16.6	560020-0500/-0520		5		9.8	10	13.7	16.6	560020-0530		5					
		7.8	8	11.7	14.6	560020-0400/-0420		4		7.8	8	11.7	14.6	560020-0430		4					
E	PLATING	5.8	6	9.7	12.6	560020-0300/-0320		3	PLATING	5.8	6	9.7	12.6	560020-0330		3	E				
		6.3		8.0	10.9	560020-0200/-0220		2		6.3		8.0	10.9	560020-0230		2					
		D	C	B	A	EMBOSSED PACKAGE ORDER NO.		CKTS		D	C	B	A	EMBOSSED PACKAGE ORDER NO.		CKTS					
CONNECTOR SERIES NO. 560020-**08								CONNECTOR SERIES NO. 560020-**18													

D	Sn BLACK						15	Sn RED							15	Sn BLUE							15	D
							14								14								14	
							13								13								13	
							12								12								12	
							11								11								11	
							10								10								10	
							9								9								9	
		11.8	15.1	19.7	22.6	560020-0821	8		11.8	15.1	19.7	22.6	560020-0822	8	11.8		15.1	19.7	22.6	560020-0823	8			
							7							7							7			
							6							6							6			
C	Sn BLACK	11.8	12	15.7	18.6	560020-0621	6	Sn RED	11.8	12	15.7	18.6	560020-0622	6	Sn BLUE	11.8	12	15.7	18.6	560020-0623	6	C		
							5							5							5			
		7.8	8	11.7	14.6	560020-0421	4		7.8	8	11.7	14.6	560020-0422	4		7.8	8	11.7	14.6	560020-0423	4			
		5.8	6	9.7	12.6	560020-0321	3		5.8	6	9.7	12.6	560020-0322	3		5.8	6	9.7	12.6	560020-0323	3			
	Sn BLACK	6.3		8.0	10.9	560020-0221	2		Sn RED	6.3		8.0	10.9	560020-0222	2		Sn BLUE	6.3		8.0	10.9	560020-0223	2	
PLATING		D	C	B	A	EMBOSSED PACKAGE ORDER NO.	CKTS	PLATING		D	C	B	A	EMBOSSED PACKAGE ORDER NO.	CKTS	PLATING		D	C	B	A	EMBOSSED PACKAGE ORDER NO.	CKTS	
CONNECTOR SERIES NO. 560020-**28								CONNECTOR SERIES NO. 560020-**48								CONNECTOR SERIES NO. 560020-**68								

A																															A

44mm or more
WIDTH TAPE

32mm WIDTH TAPE

24mm WIDTH TAPE

F
44mm or more WIDTH TAPE


4
TAPE ONLY
CENTER OF
CONNECTOR

B)

 1.75 ± 0.1

ACCUMULATIVE PITCH : 40 ± 0.2


PULL OUT DIRECTION

DIRECTION OF CONNECTOR
IN EMBOSSED TAPE

DETAIL X
(SCALE 10:1)

NOTES

1. 製品番号：
ナチュラル・錫めっき 560020-**20
ナチュラル・金めっき 560020-**30
黒・錫めっき 560020-**21
赤・錫めっき 560020-**22
青・錫めっき 560020-**23
詳細寸法については、製品単体図面を参照ください。
PART NO.
NATURAL・Sn Plating 5600020-**20
NATURAL・Au Plating 560020-**30
BLACK・Sn Plating 5600020-**21
RED・Sn Plating 5600020-**22
BLUE・Sn Plating 5600020-**23
SEE SALES DRAWING FOR CONNECTOR
2. 梱包数量： 650個/REEL
NUMBER OF CONNECTORS 650 PCS/REEL
3. リードテープ長さ
LEAD TAPE LENGTH



4. 材料
MATERIAL
キャリアテープ: ポリスチレン
CARRIER TAPE: POLYSTYRENE
トップテープ: PET, PE, PEF
TOP TAPE
リール: ポリスチレン
REEL: POLYSTYRENE
5. 一般公差
GENERAL TOLERANCES
10 UNDER: 0.2
10 OVER 30 UNDER: 0.25
30 OVER: 0.3
ANGULAR: $\pm 1^{\circ}$

REVISED EC NO: JTR2016-0015 DRAWN:KNAGA102 2016/03/01 CHK'D:HKOMATSU 2016/03/04 APPR: MAYAMOTO 2016/03/08	DESCRIPTION	0 0 0	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION			
						mm	INCH	DRAWN BY DATE		TITLE 2.0MM PITCH W/B ST. WAFER ASSY EMBOSSED TAPE PACKAGE molex				
								YTAMAKI 2014/05/23						
			4 PLACES ± --- ± ---						CHECKED BY DATE		SHEET NO. 1 OF 2			
			3 PLACES ± --- ± ---						HKOMATSU 2014/05/23					
			2 PLACES ± --- ± ---						APPROVED BY DATE					
			1 PLACE ± --- ± ---						MAYAMOTO 2014/06/30					
			0 PLACE ± --- ± ---						MATERIAL NO.		DOCUMENT NO.			
			ANGULAR ± °			SEE CHART		SD-560020-003						
			DRAFT WHERE APPLICABLE			SIZE A 3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						
MUST REMAIN WITHIN DIMENSIONS														

