

Direct Plug-In Isobar Surge Protector with 2 outlets and Black All-Metal Housing

MODEL NUMBER: ULTRABLOK



Description

For more than 20 years, America's leading companies have trusted Tripp Lite's Isobar Premium surge and noise suppressors to protect sensitive computer, networking and telecom equipment. With more than 18 million satisfied customers, the ISOBAR remains the world's #1 selling premium surge suppressor. Loaded with a generous combination of high-quality components, near indestructible all-metal case and unique noise filtration system, Isobars offer the highest levels of protection. Robust surge suppression circuits with sine wave tracking offer extreme levels of protection against the heaviest surge conditions. Isobar's unique protection system combines large toroidal chokes, HF/VHF capacitors and multiple metal oxide varistors that remove high-level surges and EMI/RFI interference. The ULTRABLOK offers 2 outlets arranged with standard wall socket spacing in a cordless direct plug-in format. Mounting tabs allow permanent connection via duplex switch plate screw. Surge suppression rated at 1410 joules/48,000 amps offers high-grade protection. Diagnostic LEDs confirm power availability, line fault and protection status. \$10,000 Ultimate Lifetime connected equipment Insurance (USA and Canada Only). PLUG/OUTLETS: Input - NEMA 5-15P; Output - 2 NEMA5-15R ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA 5-15R wall receptacle) SUPPRESSION: AC: 140V RMS Clamping/1410 joules/48,000 amps FORMAT: Direct plug-in, receptacle mount form factor

Features

- Tripp Lite's ISOBAR is the world's number one selling premium suppressor series with more than 18 million satisfied customers and a safety-tested history of 20+ years.
- 2 outlets with a direct plug-in design
- Surge energy absorption: 1410 joules/48,000 amps
- Diagnostic LEDs indicate "protection present" (green), "grounded" (red) and "line ok" (green)
- EMI/RFI noise filtering
- All-metal housing
- \$10,000 Ultimate Lifetime Insurance (USA and Canada Only) covers connected equipment

Specifications

Highlights

- 2 outlets/direct plug-in design
- 1410 joule rating—more joules mean more protection!
- Black all-metal housing with diagnostic LEDs
- Isolated filter banks remove damaging line noise
- \$10,000 Insurance for connected equipment (USA & Canada only)
- Lifetime warranty

Applications

- Ideal for premium AC protection for personal computers with peripherals, network and CAD/CAM/CAE workstations, internetworking accessories, telecommunications systems, point of sale equipment, audio/video and home theater systems in any home, office or industrial application.

Package Includes

- ULTRABLOK premium surge suppressor
- Instruction manual and warranty information



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

OVERVIEW	
Intended Application	Home/Office, Travel
OUTPUT	
Frequency compatibility	50 / 60 Hz
Output watts	1800
Circuit Breaker (amps)	15
Outlet quantity / type	2 NEMA 5-15R
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input connection type	NEMA 5-15P
Input cord length details	Direct plug-in
Voltage compatibility (VAC)	120
UPC ASSIGNMENT	
Unit Carton UPC#	037332010476
LEDS ALARMS & SWITCHES	
Diagnostic LEDs	PROTECTION PRESENT (green), LINE FAULT (red) and LINE OK (green)
SURGE / NOISE SUPPRESSION	
AC suppression joule rating	1410
AC suppression response time	NM = 0 ns. CM = <1 ns
Protection modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping voltage (RMS)	140
AC suppression surge current rating	48,000 amps
AC suppression components used	Metal oxide varistors, toroidal balanced chokes and VHF capacitors
Safe thermal fusing	Prevents unsafe conditions during extreme extended overvoltages and catastrophic occurrences
EMI / RFI filtering	40-80 dB
Immunity	Conforms to IEE 587 / ANSI C62.41
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

PHYSICAL	
Shipping Dimensions (HWD/in)	5 x 3.75 x 2.5
Shipping Dimensions (HWD/cm)	12.7 x 9.53 x 6.35
Shipping weight (lbs)	1
Shipping weight (kg)	0.45
Unit Dimensions (HWD/in)	4 x 2.5 x 2.5
Unit Dimensions (HWD/cm)	10.16 x 6.35 x 6.35
Unit weight (lbs)	.8
Unit weight (kg)	0.36
Material of construction	Metal
Housing Color	Black
Receptacle Color	Black
Style	Direct Plug-in
Form factors supported	Direct plug-in format with retaining bracket supports wall mounting directly to a standard AC wall socket
SPECIAL FEATURES	
Appearance	Attractive, all-black color scheme
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	Tested to UL1449 3rd Edition by ETL
cUL / CSA (Canada)	Approved for Canada by ETL
Approvals	Exceeds IEEE 587 category A&B specifications
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$10,000 Ultimate Lifetime Insurance

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[ULTRABLOK](#) [ISOBAR-ULTRABLOK428](#)