

# Color-Keyed®

## Narrow-Tongue Copper Lug

T&B Catalog Number:

54138NT

78620987251

Made to Order

### Description:

Copper One-Hole Lug - Standard Barrel Narrow Tongue Lug - max 35KV, #4 AWG Wire, #10 Bolt Size, Tin Plated with Inspection Hole, Gray 29

### General

Material	Copper
Finish	Tin Plated
Wire Size	#4 AWG
Number of Studs	1
Stud Size	#10
Tongue Angle	Straight
Barrel Length	Standard
Barrel Shape	Standard
Tongue Width	Narrow
Peep Hole	Y
Marking	Standard
Hole Shape	Round
Die Color	Gray
Die Code	29

### Dimension Information

A (inches)	1.312
B (inches)	0.562
C (inches)	0.365
D (inches)	0.099
E (inches)	0.365
F (inches)	0.250

### Tooling

Connector & Tooling Chart Available on Website

### Application Support

T&B Sales Drawings wsd-000288

### Notes

Dimensions given for reference only. Dimensions may vary up to +/- .030.

