


RoHS



Housing:	Out of thermoplastic (UL 94-V0, heat-resistant)
Connections:	Leaf spring connector systems, crimp contacts, copper alloy, tinned
Color:	Black
Cover:	Thermoplastic (transparent)



Part Number Artikel-Nr.	Description Beschreibung	Contact Temperature Kontakttemperatur
178.4205.000_	Complete with DFK 1.5 - 2.5 mm²	max. 130°C
178.4215.000_	Housing	—
178.6125.000_	Cover	—
178.6116.100_*	DFK-Kontakte 0.5-1.0mm²	max. 130°C
178.6116.250_*	Contacts 1.5-2.5mm²	max. 130°C
178.6116.600_*	Contacts 4.0-6.0mm²	max. 130°C

Fuse Holders