




PN 1-1 & 2-1




PN 2-6 & 1-6





PN 2-7



PN 1-7



PN 3-0



2							LB-Clip bolt	Stainless steel	-	-	9	-
	2						LB-Clip bolt	Steel	Zinc plated	Blue	8	-
		2					VS-Locking clip	Stainless steel	-	-	7	-
			2				VS-Locking clip	Steel	Zinc plated	Blue	6	-
				4			VS-Clip bolt	Stainless steel	-	-	5	-
4					4		VS-Clip bolt	Steel	Zinc plated	Blue	4	-
1							Hood HD.40.Pg.1.21	Aluminium	-	Grey	3	Special
	1		1		1		Hood HD.40.Pg.1.21	Aluminium	Aluminium oxide	Black	2	-
		1		1		1	Hood HD.40.Pg.1.21	Aluminium	-	Grey	1	-
3-0	2-7	1-7	2-1	1-1	2-6	1-6	DESCRIPTION	MATERIAL	SURFACE	COLOR	ITEM NO	NOTES

ORDERING TEXT												
HD.40.Sto-1.21.G												
HD-K.40.Sto.1.21.G												
HD.40.Sto-VS-1.21.G												
HD-K40.Sto-VS-1.21.G												
HD.40.Sto-GR.1.21.G												
HD-K40.Sto-GR-1.21.G												
HD.40.Sto-2.21-SO												

DIMENSIONS:										TOLERANCES UNLESS OTHERWISE SPECIFIED:										DWN										Tyco Electronics										Tyco Electronics, AMP GmbH																													
mm										0.130 mm ±										Schneider										D-53819, Neunkirchen, Germany																																							
										1.000 mm ±										Schweiger																																																	
										2.000 mm ±										APD										NAME																																							
										3.000 mm ±										PRODUCT SPEC										HOOD																																							
										4.000 mm ±										APPLICATION SPEC										HD.40.ST0.1.21																																							
										5.000 mm ±										SIZE										CASE CODE										DRAWING NO										RESTRICTED TO																			
										6.000 mm ±										WEIGHT										A 00779										C=1102570										-																			
MATERIAL										FINISH										CUSTOMER DRAWING										SCALE										SHEET										1 OF 1										REV. A2									