





1

[illegible]

USB3.0 A/M MOLDING TYE
(USB3.0 A/公头 成型式)
OUTER MOLD NO:HJ-CT-179
(模具编号)




DETAIL A-A

Electronic Test:

- 1.100% Test,(Open,Short,Miss Wire)
- 2.Contact Resistance:2 ohm max.
- 3.Insulation Resistance:10M ohm min.
- 4.Hi-Pot:300V DC/10ms

PIN ASSIGNMENT



NO.	NAME	Q'TY	SPECIFICATION
⑤	TUBE	4	HEAT SHRINK TUBE BLACK OD3.0* $L=6$ mm.
④	TUBE	2	HEAT SHRINK TUBE BLACK OD0.8* $L=9$ mm.
③	OUT JACKET	15g	OUTER MOLD:45P PVC COLOR:BLACK
②	CONN	2	USB3.0 A MALE TYPE SOLDER TYPE PIN-15U" INSULATION COLOR:BLUE SHELL-NICKEL
①	CABLE	1	USB3.0 [(30AWG*1P+D+AL+M)*2P+30AWG*1P+24AWG*2C+ADB PVC JACKET:BLACK OD4.8 $\pm$ 0.2

CNC Tech, LLC

Industrial Cable and Connector Technology

DRAWN BY	ZHONGHS	DRAWING NO.	
CHECKED BY		CUSTOMER	
APPROVAL BY		ITEM NO.	103-1020-BL-00100
DECIDE BY		DATE	2012-02-17
VERSIONS/EDITED	A / 0	PROJECTION	