



REV.	DATE	DESCRIPTION
NC	06/21/05	INITIAL RELEASE



NOTE:

1. CRIMPED FERRULE
HEX CRIMP SIZE .255"
2. CONTACT PIN TO SOLDER

Amphenol Connex

PART DESCRIPTION

TNC REVERSE POLARITY R/A CRIMP PLUG
(FOR BELDEN RG-8/X, TIMES LMR-240)

PART NO.

122414RP

DWG. NO. 122414RP.DWG

REV. NC

SIZE A

SCALE NA

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES. UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS ARE FOR CUSTOMER REFERENCE ONLY.

UNLESS OTHERWISE SPECIFIED, TOLERANCES FOR MILLIMETERS ARE:

0.5 - 8mm ± 0.20mm
8 - 30mm ± 0.40mm
30 - 120mm ± 0.50mm

UNLESS OTHERWISE SPECIFIED, TOLERANCES FOR INCHES ARE:

.020 - .315 = ± 0.007"
.315 - 1.180 = ± 0.015"
1.180 - 4.724 = ± 0.020"

DO NOT SCALE DRAWING

APPROVALS

DATE

DRAWN G.R.S.

06/21/05

CHECKED

ISSUED

SHEET 1 OF 1

CAD FILE

C:/122/122414RP.DWG