


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PART NUMBER	LENGTH (MINIMUM)	PACKAGE TYPE	WEIGHT
FG3**5.0-A	5 FEET	COIL	.246 lb/ft [.37 g/mm]
FG3**50.0-A	50 FEET	COIL	.246 lb/ft [.37 g/mm]

NOTES:

- SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
- DIMENSIONS IN PARENTHESIS ARE IN METRIC.
- NOMINAL WALL THICKNESS IS .08 [2.0]
- TO APPLY PART:
 - CUT FLOORGUARD TO DESIRED LENGTH.
 - INSERT WIRES INTO FLOORGUARD.
 - APPLY TAPE TO FLOORGUARD. (TAPE IS TO BE CENTRALLY LOCATED ON THE FLOORGUARD AS SHOWN ON THE DRAWING)
 - REMOVE RELEASE LINER FROM TAPE AND PLACE FLOORGUARD ON A CLEAN, DRY SURFACE.
 - APPLY PRESSURE TO ENTIRE LENGTH OF FLOORGUARD TO OBTAIN MAXIMUM ADHESION.
- NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE PRODUCTS MAY BE APPLIED AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL.

CAD FILENAME/LAYERS 09D054BR_DC_FG3/00A

PANDUIT CORP TINLEY PARK, ILLINOIS

FLOORGUARD FG3

CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:

1.X1 ±
1.XX ± .03 [.8]

1.XXX1 ±
ANGLES ±

UNLESS OTHERWISE SPECIFIED, ALL
DIMENSIONS ARE GIVEN IN INCHES,
THIRD ANGLE PROJECTION

DRAWN BY BDK

MAT'L/COLOR:

SCALE NONE

DATE 11.17.10

FLEXIBLE
VINYL

DRAWING NO.
09D054BR-DC

DWG
A
SIZE

R 12.29.10 BDK JBN RELEASED TO PRODUCTION

09D054BR-DC PATR RTF I

REV DATE BY CHK DESCRIPTION

ECN CHK CUST SUP