



ALL TOLERANCES = ±0.004 [±0.10]
UNLESS OTHERWISE INDICATED



BACK SHELL KIT INCLUDES:

- 2 - BACK SHELL HALVES
- 2 - 4-40 MATING SCREWS
- 2 - SADDLE WASHERS
- 2 - HOUSING SCREWS
- 2 - HOUSING NUTS
- 1 - GROMMET TREE - VARIOUS SIZES
(NON-CONDUCTIVE GROMMETS)

MATERIAL: DIE-CAST ZINC ALLOY
PLATING: NICKEL
OPERATING
TEMPERATURE: -45°C TO + 120°C

979-037-030 R 12 1

SERIES _____

POSITIONS _____

009 _____

015 _____

025 _____

037 _____

050 _____

MATERIAL _____

030 = ZINC _____

RoHS COMPLIANT _____

R = HIGH TEMP. PROCESS _____

PLATING _____

12 = NICKEL _____


PUT-UPS _____

1 = KIT _____


DO NOT SCALE FROM DRAWING

RoHS COMPLIANT




	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: C. SMITH		DATE: 03-18-10		
		CHECKED:		DATE:		
NorComp		SCALE: 1 : 1		SHEET 1	OF 1	REV 2
		DWG NO. 979-037-030R121				



MATING SCREW



HOUSING SCREW




SADDLE WASHER

HOUSING NUT

ALL HARDWARE:

MATERIAL = BRASS
PLATING = NICKEL
TOLERANCE = ± 0.002 [± 0.05]
SCALE = 2 : 1

RoHS COMPLIANT



MATERIAL: NON CONDUCTIVE PVC - BLACK
TOLERANCE = ± 0.010 [± 0.25]
SCALE = 1 : 1

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:	C. SMITH
--------	-----------------

DATE:	04-20-10
-------	----------

CHECKED:

DATE:

SCALE:
AS SHOWN

SHEET	OF
2	2

REV
2

DWG NO.	
---------	--

979-037-030R121

NorComp