

# Lock Nuts, Polyamide

## Material:


- Polyamide 6
- 25 % Glass fiber Reinforced

## Characteristic feature:


- PG / metric and NPT thread

### Temperature Range PA

-30 to 120°C (-22 to 248°F)



| Thread                                   | Thickness (E)<br>mm | SW<br>mm | Cat. No.<br>Light grey | Cat. No.<br>Black | Std.<br>Pk. |
|------------------------------------------|---------------------|----------|------------------------|-------------------|-------------|
| <b>PG (once according to DIN 46 320)</b> |                     |          |                        |                   |             |
| PG 7                                     | 5                   | 19       | 7211881                | 7211851           | 50          |
| PG 9                                     | 5                   | 22       | 7211882                | 7211852           | 50          |
| PG 11                                    | 5                   | 24       | 7211883                | 7211853           | 50          |
| PG 13.5                                  | 6                   | 27       | 7211884                | 7211854           | 50          |
| PG 16                                    | 6                   | 30       | 7211885                | 7211855           | 50          |
| PG 21                                    | 6.5                 | 36       | 7211886                | 7211856           | 20          |
| PG 29                                    | 7.5                 | 46       | 7211887                | 7211857           | 20          |
| PG 36*                                   | 8                   | 60       | 7211888                | 7211858           | 10          |
| PG 42*                                   | 9                   | 65       | 7211889                | 7211859           | 5           |
| PG 48*                                   | 9.5                 | 70       | 7211890                | 7211860           | 5           |
| <b>Metric</b>                            |                     |          |                        |                   |             |
| M 12 x 1.5                               | 5                   | 19       | 7211979                | 7211974           | 50          |
| M 16 x 1.5                               | 5                   | 22       | 7211980                | 7211975           | 50          |
| M 20 x 1.5                               | 5                   | 24       | 7211981                | 7211976           | 50          |
| M 25 x 1.5                               | 6                   | 30       | 7211982                | 7211977           | 50          |
| M 32 x 1.5                               | 7.5                 | 38       | 7211983                | 7211978           | 50          |
| M 40 x 1.5                               | 8                   | 50       | 7211984                | 7211990           | 20          |
| M 50 x 1.5*                              | 9                   | 60       | 7211985                | 7211991           | 10          |
| M 63 x 1.5*                              | 10                  | 75       | 7211986                | 7211992           | 5           |
| <b>NPT</b>                               |                     |          |                        |                   |             |
| NPT 3/8"                                 | 5                   | 22       | 7211485                | 7211495           | 50          |
| NPT 1/2"                                 | 6                   | 27       | 7211486                | 7211496           | 20          |
| NPT 3/4"                                 | 6.5                 | 36       | 7211487                | 7211497           | 20          |
| NPT 1"                                   | 7                   | 41       | 7211488                | 7211498           | 20          |



\* Not glass fiber reinforced.