

Heavy Duty Power Cord, 15A, 14AWG (IEC-320-C19 to IEC-320-C14) 10-ft.

MODEL NUMBER: **P047-010**



Highlights

- C19 to C14 Power Cable, 10 ft.
- 14 AWG x 3C - 15A - 250V
- RoHS Compliant

Package Includes

- C19 to C14 Power Cable, 10 ft.

Description

Tripp Lite Heavy Duty C19 to C14 10 ft. Power Cable. Constructed with 3 x 14 AWG copper conductors, fully molded ends, 100-250V / 15A rating.

Features

- Molded, Heavy-Duty Power Cable, 10 ft.
- IEC-60320-C19 to IEC-60320-C14
- 14 AWG x 3C, SJT, 15A, 100-250 Volt
- RoHS Compliant

Specifications

OVERVIEW	
Intended Application	Powering Devices
Cable Type	POWER
Model Type	Power Cords
INPUT	
Cable Length (ft.)	10
Cable Length (m)	3.05
UPC ASSIGNMENT	
Unit Carton UPC#	037332140890

PHYSICAL	
Color	Black
Style	Power Cables
CONNECTIONS	
Connector A	IEC-320-C19
Connector B	IEC-320-C14
Number of Connectors	2
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.