


CAD GENERATED DRAWING – NO PENCIL CHANGES ALLOWED

PART NUMBER	CURRENT RATING (A)	BODY COLOR	RATED VOLTAGE		% OF RATED CURRENT	OPENING TIME	
						MIN	MAX
0283020.MXJ-B	20	LT. BLUE	32V		110%	14,400 SEC.	-
0283030.MXJ-B	30	PINK			200%	5 SEC.	100 SEC.
0283040.MXJ-B	40	GREEN			350%	0.2 SEC.	7 SEC.
0283050.MXJ-B	50	RED			600%	0.04 SEC.	1 SEC.
0283060.MXJ-B	60	YELLOW					
0283070.MXJ-B	70	BROWN					
0283080.MXJ-B	80	BLACK					
0283100.MXJ-B	100	BLUE					
0283120.MXJ-B	120	WHITE					
0283140.MXJ-B	140	REDDISH BROWN					



METRIC

	UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES
	UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.
	DENOTES CRITICAL CHARACTERISTICS.
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE
	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

[illegible]