

LP-LED LP-LED MV and LP-LED 110/230V



CE – certified to EMC directive 2004/108/EC.
Complies with low voltage directive 2006/95/EC.
High voltage transient and polarity reversal protected.
Operating temperature: –20°C to + 55°C.



Mains 110/230V	amber >17cd red >33cd (flashing mode)	65 flashes/min 6 bursts/flash	85–265 Vac	IP67	100gms
Multivoltage MV			10–100Vdc		

Features:

A low profile LED beacon with low power consumption.

- Multivoltage 10–100Vdc, and mains 110Vac and 230Vac versions
- Flashing and continuously lit modes
- Clear lens with coloured LEDs
- Low power consumption
- 3 year guarantee
- Weatherproof to IP67

Materials:

Polycarbonate lens and base. ROHS compliant.

Accessories:

FX1 mounting box



FX2 mounting base



FX40 mounting bracket



Product	<i>i</i> flashing	<i>i</i> constant	Amber	Red
Mains 110/230V	15mA @ 110Vac 10mA @ 230Vac		447002	447003
Multivoltage MV	110mA @ 12Vdc 55mA @ 24Vdc 35mA @ 50Vac 25mA @ 100Vac	80mA @ 12Vdc 40mA @ 24Vdc 25mA @ 50Vac 20mA @ 100Vac	445002	445003

76 mm

48 mm

3 x 5.5mm holes

22.5 mm

45 mm