


Capacitor, ceramic, 0.047 uF, +/-10% Tol, 50V, X7R, Lead Spacing=0.2"



Dimensions (in)

ID	Dimension	Tolerance
W	0.2	
H	0.26	max
T	0.125	max
S	0.2	+/-0.03
LL	0.276	min
F	0.02	+0.004/-0.001
G	0.031	ref

Specifications

Manufacturer:	KEMET
Capacitance:	0.047 uF
Lead Spacing:	0.2"
Voltage:	50V
Temperature Coefficient:	X7R
Tolerance:	+/-10%
Body Type:	Radial Conformal
Lead Type:	Standard Leads
Lead Form:	Hockey Stick
Termination Type:	Tin
Package Kind:	Bulk
Package Type:	Bag
Package Quantity:	500