

24V Flexiprint Silicone IP67

RGB (PLCC6)

Specifications

Voltage	24V
Current	3x1A
Wattage	14.4W/m (3x4.8W/m)
Number of LED's	300pcs
Length of Stripe	5meter
Operating Temperature	-25°~+60°C
Storage Temperature	-40°~+80°C
Viewing angle	110°

Benefits


IP67 protection
Adhesive tape on backside
RoHS compliant



Electrical and Optical Characteristics (Ta=25°C)

Part-Number	Colour	Wavelength	Intensity lm
FPS-F02D-500	 red	624 nm	600-650
	 green	518 nm	900-930
	 blue	471 nm	460-470

Dimensions



Thickness: 5.8 mm

Thickness endings: 6.4 mm

Adapter with cable 250 mm included

1. All specifications according to information from our manufacturers, without additional guarantee on our part
2. All dimensions are in millimetres
3. Tolerance is ± 0.2 mm unless otherwise specified
4. Specifications are subject to change without notice