




UNIT: mm



PIN ASSIGNMENT:



Electrical test:
1. 100% short, open, miswire test
2. Conduct resistance: 2 Ohm(max)
3. Insulation resistance: 10Mohm(min)
4. dielectric test: DC 300V



1PCS/PE BAG

CnC Tech, LLC Industrial Cable and Connector Technology				
⑨	PE BAG	1/10	CLEAR SIZE: 280*330*0.05mm	PRINT BLACK"MADE IN CHINA"+ "10PCS"
⑧	PE BAG	1	CLEAR SIZE: 130*230*0.05mm	PRINT BLACK"MADE IN CHINA"
⑦	TIE	2	WHITE L=100mm	
⑥	IN JACKET	3g	CLEAR LDPE (MOULD NO: NM-027)	
⑤	OUT JACKET	7g	BEIGE (IV-29#) PVC-40P (MOULD NO: WM-83)	
④	OUT JACKET	6g	BEIGE (IV-29#) PVC-40P (MOULD NO: WM-40)	
③	CABLE	1	BEIGE (IV-29#) USB1.1 UL2725 28#/1P+24#/2C+AEB OD: 4.7mm L=3000 ± 10mm	
②	CONN	1	USB A FEMALE SHELL: NICKEL PIN G/F SHORT TYPE INSULATOR COLOR: WHITE	
①	CONN	1set	USB A MALE SHELL: NICKEL PIN G/F 3PCS TYPE INSULATOR COLOR: WHITE	
NO.	NAME	Q' TY	SPECIFICATION	
VERSIONS/EDITION		A/0	PROJECTION	