



UHMW Polyethylene Tape

5425

Technical Data

July, 2010

Product Description

3M™ UHMW Polyethylene Tape 5425 is a film coated with a special acrylic adhesive that is resistant to many solvents.

Product Construction

Backing	Adhesive	Liner	Color	Standard Roll Length
Ultra-high molecular weight polyethylene	Acrylic	55# densified kraft	Translucent	36 yds. (32.9 m)

Typical Physical Properties

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

ASTM Test Method		
Adhesion to Steel:	30 oz./in. width (33 N/100 mm)	D-3330
Tensile Strength:	45 lbs./in. width (788 N/100 mm)	D-3759
Elongation at Break:	100%	D-3759
Backing Thickness:	3.0 mils (0.08 mm)	D-3652
Total Tape Thickness: (without liner)	5.0 mils (0.13 mm)	D-3652
Liner Thickness:	3.2 mils (0.08 mm)	D-3652
Temperature Use Range:	-30° to 225°F (-34° to 107°C)	

Features

- Acrylic adhesive is a firm high solvent and oil resistant adhesive which bonds best to high surface energy materials.
- UHMW polyethylene is a thermoplastic that has a unique combination of properties which make it ideal for many tough impact wear or sliding applications. Within its operational temperature range, UHMW polyethylene tape can provide the following advantages:
 - A. Outstanding abrasion resistance:** Will outwear many types of PTFE and other materials in sliding applications.
 - B. Low coefficient of friction:** Exceeded only by the PTFE's.
 - C. Self-lubricating:** Can often be used where lubrication is not possible because of contamination.
 - D. Sound damping:** High energy absorption capacity helps reduce noise levels in machinery and equipment.

3M™ UHMW Polyethylene Tape

5425

Application Ideas

- Abrasion protection for rubber fuel cells.
- Gaskets exposed to many corrosive chemicals.
- Spiral wrap wire harness to resist hydraulic fluids.
- Dissimilar metal separation to help prevent wear and chemical corrosion.
- Excellent for wear surfaces where transparency is needed.
- Guide rails and chutes requiring a more durable, solvent resistant slide surface.

Storage

Store under normal conditions of 60° to 80°F (16° to 27°C) and 40 to 60% R.H. in the original carton.

Shelf Life

To obtain best performance, use this product within 18 months from date of manufacture.

Technical Information

The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

Product Use

Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty, Limited Remedy, and Disclaimer

Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability

Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

ISO 9001:2000

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001:2000 standards.



Industrial Adhesives and Tapes Division

3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
800-362-3550 • 877-369-2923 (Fax)
www.3M.com/industrial



Recycled Paper
40% pre-consumer
10% post-consumer

3M is a trademark of 3M Company.
Printed in U.S.A.
©3M 2010 70-0709-5119-2 (7/10)