

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2003

© COPYRIGHT 2003

BY -

ALL RIGHTS RESERVED.

14.2

11.5

5.5

26.4

5.5

PITCH (PASSO)

2.7

CPA STROKE (CORSA CPA)

6.1

18.5

1745079-1

REV. A

A047

tygo 567

13.8

3.2

20.8

2

4

1

6

3

20.8

10.7

31.5

1

4

3

2

SCALE 2:1

P/N 1745078-2

HOUSING: PBT GF COLOR BLACK
(CONNETTORE: PBT CARICATO VETRO,NERO)

4

PLUGGED CAVITIES (Nr. 2-5)
(CAVITA' TAPPATE Nr. 2-5)

FRONT VIEW
(VISTA FRONTALE)

BACK VIEW
(VISTA POSTERIORE)

SCALE 2:1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN M. POLIZZI 06SEP2005

CHK O. CANUTO 06SEP2005

APVD A. GENIA 06SEP2005

PRODUCT SPEC 108-20274

APPLICATION SPEC -

WEIGHT -

CUSTOMER DRAWING

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±0.5

1 PLC ±0.3

2 PLC ±0.1

3 PLC ±

4 PLC ±

ANGLES ±1°

FINISH

SEE TABLE (VEDI TABELLA)

NAME 6 POS AMP MCP 2.8K RECEPTACLE CONNECTOR ASSY (ASSEMBLATO 6 VIE PER CONTATTO AMP MCP2.8K)

SIZE A2

CAGE CODE -

DRAWING NO C-1745078

RESTRICTED TO -

SCALE 3:1

SHEET 1

OF 1

REV A1

TE Connectivity

1

2

3

4

5

6

7

8

9

10

11

12

13

14

15

16

17

18

19

20

21

22

23

24

25

26

27

28

29

30

31

32

33

34

35

36

37

38

39

40

41

42

43

44

45

46

47

48

49

50

51

52

53

54

55

56

57

58

59

60

61

62

63

64

65

66

67

68

69

70

71

72

73

74

75

76

77

78

79

80

81

82

83

84

85

86

87

88

89

90

91

92

93

94

95

96

97

98

99

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED FOR PRODUCTION	17OCT2007	M.P.	R.M.
	A1	ECO-16-007463	17MAY2016	M.P.	M.G.

1745079-1

REV. A

A047

tygo 567

SCALE 2:1

1) FEMALE CONNECTOR SUPPLIED WITH SECONDARY LOCK AND C.P.A. PRE-ASSEMBLED

(CONNETTORE PORTAFEMMINE FORNITO CON AGGANCIO SECONDARIO E C.P.A. PRE-MONTATI)

2) CAVITY SUITABLE FOR AMP MCP 2.8K CONTACTS TIN PLTD:
P/N 0-1241392-1 WIRE RANGE: 0.35 mm², WIRE SEAL P/N 963294-1
P/N 0-1241394-1 WIRE RANGE: 0.5±1.0 mm², WIRE SEAL P/N 963294-1
P/N 0-1241396-1 WIRE RANGE: >1.0±1.5 mm², WIRE SEAL P/N 963293-1
P/N 0-1241396-1 WIRE RANGE: 2.5 mm², WIRE SEAL P/N 963292-1
CAVITY PLUG P/N 828922-1

(CAVITA' ADATTA PER CONTATTI AMP MCP 2.8K STAGNATO:
P/N 0-1241392-1 RANGO FILO 0.35 mm², GOMMINO P/N 963294-1
P/N 0-1241394-1 RANGO FILO 0.5±1.0 mm², GOMMINO P/N 963294-1
P/N 0-1241396-1 RANGO FILO >1.0±1.5 mm², GOMMINO P/N 963293-1
P/N 0-1241396-1 RANGO FILO 2.5 mm², GOMMINO P/N 963292-1
TAPPO CAVITA' P/N 828922-1

3) FOR COUNTERPART INTERFACE DRAWING SEE CUSTOMER DRAWING P/N 114-18642.
WIRE TO WIRE COUNTERPART P/N 1452324

(PER IL DISEGNO DELLA CONTROPARTE DI INTERFACCIA, VEDERE DISEGNO CLIENTE P/N 114-18642.
CONTROPARTE VOLANTE P/N 1452324)

1471-9 (3/13)